

740nm Dual Stage Free-Space Optical Isolator



Stock **#35-982** **1 In Stock**

- 1 + MRP ₹5,35,726

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | ₹5,35,726 each |
| Qty 5+ | ₹4,82,154 each |
| Need More? | Request Quote |

Product Downloads

General

Dual Stage Optical Isolator **Type:**

Faraday **Style:**

Physical & Mechanical Properties

4.7 **Clear Aperture CA (mm):**

Optical Properties

Minimum Transmission (%):

>80

Transmission (%):

90

Design Wavelength DWL (nm):

740

Wavelength Range (nm):

720 - 760

Damage Threshold, By Design:

40 W, 4 kW/cm² @ DWL

Typical Isolation at Design Wavelength (dB):

67

Minimum Isolation at Design Wavelength (dB):

>60

Environmental & Durability Factors

Operating Temperature (°C):

+15 to +40

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Up to 67 dB Isolation for Ultimate Stability
- Up to 92% Transmission for Maximum Power
- 4.7mm Input Aperture

Free-Space Optical Isolators incorporate a Faraday Rotator and are specifically designed and manufactured to provide superior performance with high isolation, transmission, and power densities. Each option effectively reduces feedback in the external cavity of diode laser systems and blocks reflections from free-space fiber coupling. Free-Space Optical Isolators increase power stabilization in optical systems and also eliminate feedback-induced damage to sensitive optical components. These isolators enable state of the art protection for the most stable lasers in the world and are ideal for demanding laser applications.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)