


750 - 900nm (Ti:Sapphire), 4-6mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- π Shaper_TiS_Q-5

See More by [AdlOptica](#)



Stock #25-849 **1 In Stock**

1 ₹2,76,300

ADD TO CART

Volume Pricing	
Qty 1-4	₹2,76,300 each
Qty 5+	₹2,45,700 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Focal- π Shaper_TIS_Q-5 **Model Number:**

Beam Shaper **Type:**

[#12-322](#) **Compatible Adapter:**

Physical & Mechanical Properties

20 **Clear Aperture CA (mm):**

42.00 **Diameter (mm):**

29.00 **Length (mm):**

50 **Weight (g):**

2.5 - 4 **Input Beam Diameter, $1/e^2$ (mm):**

Optical Properties

750, 900 **Design Wavelength DWL (nm):**

>99 **Transmission (%):**

750 - 900 **Wavelength Range (nm):**

TEM₀₀ **Input Beam Mode:**

<1.5 **Typical Input Beam Mode Quality, M²:**

±20 **Input Beam Divergence (mrad):**

Electrical

0.2 **Maximum Input Power, CW (kW):**

Threading & Mounting

M30 x 0.75 **Inner Thread:**

M30 x 0.75 **Outer Thread:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

PRODUCT DETAILS

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica \$\pi\$ Shaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal- π Shaper (π Shaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the π Shaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal- π Shapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

TECHNICAL INFORMATION

