

[See all 32 Products in Family](#)

# 750 - 900nm (Ti:Sapphire), 6-9mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- $\pi$ Shaper\_TiS\_Q-7.5

See More by [AdiOptica](#)



Stock #25-850 **1 In Stock**

⊖ 1 ⊕ MRP ₹3,35,516

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹3,35,516 each
Qty 5+	₹2,98,237 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

Focal- $\pi$ Shaper\_TiS\_Q-7.5 **Model Number:**  
Beam Shaper **Type:**

Compatible Adapter:

#12-322

## Physical & Mechanical Properties

Length (mm):

29.00

Weight (g):

50

Clear Aperture CA (mm):

20

Diameter (mm):

42.00

Input Beam Diameter,  $1/e^2$  (mm):

4 - 6

## Optical Properties

Transmission (%):

>99

Design Wavelength DWL (nm):

750, 900

Wavelength Range (nm):

750 - 900

Input Beam Mode:

TEM<sub>00</sub>

Typical Input Beam Mode Quality, M<sup>2</sup>:

<1.5

Input Beam Divergence (mrad):

±20

## Electrical

Maximum Input Power, CW (kW):

0.2

## Threading & Mounting

Inner Thread:

M30 x 0.75

Outer Thread:

M30 x 0.75

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 250:

Compliant

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

## Technical Information

