

[See all 102 Products in Family](#)

## 75mm Diameter x 50mm FL , MgF<sub>2</sub> Coated, Aspheric Condenser Lens



Stock **#15-542** **3 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ ₹8,486

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹8,486 each
Qty 11-49	₹7,551 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Condenser Lens **Type:**

### Physical & Mechanical Properties

75.00 +0.0/-0.5 **Diameter (mm):**

≤20 **Centering (arcmin):**

**Clear Aperture CA (mm):**

72

Edge Thickness ET (mm):

3.0

Center Thickness CT (mm):

30.00 ±0.50

Bevel:

Protective as needed

Diameter of Asphere (mm):

75.0

Shape of Back Surface:

Plano

### Optical Properties

Effective Focal Length EFL (mm):

50.00

Numerical Aperture NA:

0.75

Back Focal Length BFL (mm):

30.50

Substrate:

[B270](#)

Focal Length Tolerance (%):

±7

Coating:

MgF<sub>2</sub> (400-700nm)

Coating Specification:

R<sub>avg</sub> ≤ 1.75% @ 400 - 700nm

Surface Quality:

80-50 (typical)

f#:

0.7

Radius R<sub>2</sub> (mm):

Plano

Wavelength Range (nm):

400 - 700

Conjugate Distance:

Infinite

### Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:

[Compliant](#)

Country of Origin:

Germany

Imported By:


Edmund Optics India Private Limited


## Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

## Technical Information





## Coating Curves

;