

[See all 67 Products in Family](#)

LightPath 355110 | 780nm Alignment, 0.40 NA Fiber Collimator w/ FC/PC Connector

See More by [Lightpath®](#)



780nm Alignment, 0.40 NA Fiber Collimator w/ FC Connector, #64-771

Stock **#64-771** 20+ In Stock

-

1

+

₹16,830

ADD TO CART

Volume Pricing	
Qty 1-10	₹16,830 each
Qty 11-25	₹14,850 each
Qty 26-49	₹13,950 each
Need More?	Request Quote

Product Downloads

General	
355110	Lightpath Lens Code:
Fiber Collimator	Type:
#87-126	Lens Included:

Physical & Mechanical Properties	
5.00	Clear Aperture CA (mm):
Protective as needed	Bevel:
304L Stainless Steel Housing	Construction:
11.00	Housing Diameter (mm):
13.00	Housing Length (mm):
Optical Properties	
6.24 @ 780nm	Effective Focal Length EFL (mm):
0.40	Numerical Aperture NA:
D-ZLaF52LA	Substrate: 
BBAR (600-1050nm)	Coating:
R _{abs} <1.0% @ 600 - 1050nm	Coating Specification:
40-20	Surface Quality:
1.25	f#:
600 - 1050	Wavelength Range (nm):
Infinite	Conjugate Distance:
780	Alignment Wavelength (nm):
< 0.070	Transmitted Wavefront Error (λ, RMS):

Hardware & Interface Connectivity	
FC/PC	Connector:

Threading & Mounting	
M11 x0.5	Mount:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

Technical Information

