

TECHSPEC® 785nm, 12.5mm Diameter, Raman Edge Filter



Stock #86-228 5 In Stock

-

1

+

₹40,482

ADD TO CART

Volume Pricing	
Qty 1-9	₹40,482 each
Qty 10+	₹33,709 each
Need More?	Request Quote

Product Downloads

General

Longpass Filter

Type:

Bandwidth (nm): >700

Note:

Physical & Mechanical Properties

12.50 +0.0/-0.1

Diameter (mm):

±0.1

Thickness Tolerance (mm):

>80	Clear Aperture (%):
Optical Properties	
0 ±2	Angle of Incidence (°):
≥6.0	Optical Density OD (Average):
792.80	Cut-On Wavelength (nm):
785	Design Wavelength DWL (nm):
Substrate: □	
Fused Silica (Corning 7980)	
Coating:	
Hard Coated	
Surface Quality:	
60-40	
Transmission (%):	
>90	
Transition Width (nm):	
<7.8	
Transmitted Wavefront, RMS:	
<λ/4 @ 633nm	
Coating Specification:	
T _{abs} ≥93% @ 804 - 900nm T _{avg} ≥90% @ 804 - 1500nm	
Wavelength Range (nm):	
785 - 1500	
Laser Blocking Wavelength (nm):	
785.00	
Threading & Mounting	
3.5	Mount Thickness (mm):
Environmental & Durability Factors	
Durability:	
Environmental: ML-STD-810F Physical: ML-C-48497A	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	
Country of Origin:	
United States	
Imported By:	
Edmund Optics India Private Limited	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Transmission for Detecting Weak Signals
- Deep Blocking for Maximum Laser Rejection
- Ideal for Raman Spectroscopy or Life Science Instrumentation

TECHSPEC® Raman Longpass Edge Filters are single filter solutions for reducing spectral noise in Stokes shift applications. These filters are designed to create sharp transitions between transmitted Raman signals and blocked laser wavelengths. Designed to detect even the smallest Raman shifts, TECHSPEC Raman Longpass Edge Filters are ideal for integration into Raman spectroscopy or confocal microscopy systems. The hard coated design offers superior transmission characteristics than comparable traditional coated filters.

Compatible Mounts

;