

[See all 24 Products in Family](#)

# CO<sub>2</sub> Flat Top Beam Shaper 7mm | πShaper 7\_7\_10.6

See More by [AdlOptica](#)



Stock #34-259 **2 In Stock**

- 1 + MRP ₹7,18,822

Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | ₹7,18,822 each                |
| Qty 5-10       | ₹6,47,131 each                |
| Qty 11+        | ₹6,10,807 each                |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

### General

πShaper 7\_7\_10.6 **Model Number:**

Beam Shaper **Type:**

Flat Top **Style:**

## Physical & Mechanical Properties

143.00 **Length (mm):**

<270 **Weight (g):**

39.00 **Diameter (mm):**

## Optical Properties

7 **Entrance Beam Diameter,  $1/e^2$  (mm):**

10600 **Design Wavelength DWL (nm):**

10000 - 11000 **Wavelength Range (nm):**

20 mJ/cm<sup>2</sup> @ 5ns (typical) **Damage Threshold, By Design:**

7.0 **Output Diameter, FWHM (mm):**

20 mJ/cm<sup>2</sup> @ 5ns (typical) **Damage Threshold, Pulsed:**

## Threading & Mounting

M27 x 1 **Mounting Threads:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

Germany **Country of Origin:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000 **Imported By:**

## Product Details

- Convert Gaussian Beam Profile to Flat Top Profile
- Near 100% Efficiency
- No Internal Focusing Enables High Power Laser Input
- [AdlOptica Focal- \$\pi\$ Shaper Q Flat Top Beam Shapers](#) Also Available

AdlOptica  $\pi$ Shaper (piShaper) Flat Top Beam Shapers are refractive field mapping optical systems that convert collimated Gaussian input beams into collimated flat top beams with a uniform intensity distribution and flat phase front. Due to the field mapping optical design, the even intensity distribution of the converted beam is stable over great distances making it ideally suitable for holography, microscopy, system integration and ultrafast applications. With no internal focusing, they are also the perfect solution in applications such as material micromachining, welding, and engraving that require high power lasers. These AdlOptica  $\pi$ Shaper Flat Top Beam Shapers are offered in common YAG, fiber laser, and CO2 laser sources, operating over a defined wavelength range for laser tuning. Achromatic versions are designed to be used with multiple laser sources.

**Note:** Focusing a flat-top beam after a  $\pi$ Shaper results in loss of the flat top profile. [AdlOptica Focal- \$\pi\$ Shaper Q Flat Top Beam Shapers](#) are available for applications that require a focused flat top spot.

**LASER OPTICS** MADE BY EDMUND OPTICS®

[LEARN MORE](#)

## Technical Information

Example of beam shaping for TEM<sub>00</sub> Laser

