

[See all 23 Products in Family](#)

Flea3/Grasshopper3 8-pin GPIO Hirose Connector Cable, 1m

See More by [Teledyne FLIR](#)



Flea3/Grasshopper3 8-pin GPIO Hirose Connector Cable, 1m, #88-059



Stock **#88-059** 7 In Stock

-

1

+

₹6,018

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹6,018 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Type:
Camera Accessory

Hardware & Interface Connectivity

Length of Cable (m):

Connector:	
Male	
Regulatory Compliance	
Certificate of Conformance:	
View	
Country of Origin:	
Canada	
Imported By:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Feature High Resolution, High Sensitivity Sensors
- High Frame Rates Driven by USB 3.0 Interface
- Includes Image Capture Software and SDK



Teledyne FLIR IIS Grasshopper®3: Machine Vision area scan camera

The **Grasshopper®3** offers a cost-effective, powerful and easy-to-use alternative to Camera Link and dual GigE LAG solutions.

The **Grasshopper®3** camera line combines the benefits of CCD with the affordability and data throughput of either USB 3.0 or GigE interfaces. This high-performance camera model provides a range of characteristics with either CMOS or CCD sensors. Its FPGA and frame buffer-based architecture provides optimal reliability, a rich set of features, and a full image processing pipeline including color interpolation, gamma, and lookup table functionality.

Note: USB 3.0 cable (sold separately) is required for operation. Optional power supply ([#86-784](#)) available. Software available for [download](#). FLIR was previously known as Point Grey.

Features

- Compact form factor
- USB 3.0 models with resolutions from 2.3 to 12 Megapixel sensors
- GigE interface model at 2.3 Megapixel for high bandwidth performance
- Various high-resolution, large format CCD and CMOS sensor options
- Color transformation tools for true-to-life color
- GigE models feature PoE for simplified setup and maintenance
- Spinnaker SDK and code samples

Applications

- Factory automation
- 3D Measurement
- Flat Panel Inspection
- Life science instrumentation
- Biometrics kiosk solutions
- Ophthalmology
- Intelligent traffic systems