


[See all 9 Products in Family](#)

**TECHSPEC® 800 - 1150nm, 25.4mm Dia. Ultrafast-Enhanced Silver, Silicon, Laser Mirror**



Stock #90-195 NEW **3 In Stock**

₹13,140

ADD TO CART

Volume Pricing	
Qty 1+	₹13,140 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Flat Mirror Type:

**Physical & Mechanical Properties**

<3 Parallelism (arcmin):

90 Clear Aperture (%):

Commercial Polish Back Surface:

Diameter (mm):

25.40 +0.00/-0.10

6.35 ±0.10 **Thickness (mm):**

Ground, protective bevel as needed **Edges:**

## Optical Properties

40-20 **Surface Quality:**

Ravg >99% @ 850 - 1150nm, 0° Rs >99% @ 800 - 1150nm, 45° Rp >98.5% @ ~850 - 1100nm, 45° **Coating Specification:**

0 ±30 fs<sup>2</sup> @ 800-1100 nm **GDD Specification:**

800 - 1150 **Wavelength Range (nm):**

λ/10 **Surface Flatness (P-V):**

Ultrafast-Enhanced Silver **Coating Type:**

Ultrafast-Enhanced Silver (800-1150nm) **Coating:**

Optical Grade Silicon **Substrate:** □

0.35 J/cm<sup>2</sup> @ 1030nm, 200fs, 1 pulse (typical) 0.10 J/cm<sup>2</sup> @ 1030nm, 200fs, 100Hz, 1000 pulses (typical) **Damage Threshold, Reference:** □

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

Vietnam **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

## Product Details

- Silicon Substrate for Thermally Demanding Ultrafast Setups
- Ideal For Ti:Sapphire- and Yb-Based Ultrafast Laser Systems
- Designed For Ultrafast Pulse Reflection Where Low Dispersion is Critical
- < 30fs<sup>2</sup> GDD in Target Wavelength Ranges

TECHSPEC® Ultrafast-Enhanced Silver Coated Silicon Laser Mirrors combine a broadband enhanced-silver coating with low group delay dispersion (GDD) for ultrafast pulse applications. These mirrors are designed for systems where maintaining pulse fidelity is critical, and reflectivity and GDD are characterized across the specified wavelength range of 600 – 1000nm or 800 – 1150nm. These silicon substrate mirrors feature higher thermal conductivity than comparable [fused silica substrate mirrors](#), which helps evenly distribute absorbed heat in thermally demanding optical setups. TECHSPEC® Ultrafast-Enhanced Silver Coated Silicon Laser Mirrors are ideal for broadband ultrafast beam delivery where high reflectivity, controlled dispersion, and a thermally robust substrate are desired.