

[See all 36 Products in Family](#)

## 800nm, 12.5mm Dia., OD 2.0 Shortpass Filter



OD 2.0 Shortpass Filters

Stock #15-252 **20+ In Stock**

1 MRP ₹9,080

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-9    | ₹9,080 each                   |
| Qty 10-25  | ₹8,173 each                   |
| Qty 26-49  | ₹7,567 each                   |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

Shortpass Filter **Type:**

### Physical & Mechanical Properties

12.50 +0.00/-0.20 **Diameter (mm):**

**Thickness (mm):**

2.00 ±0.10

90 **Clear Aperture (%):**

**Physical Durability:**  
ML-C-48497A, Section 3.4.1

## Optical Properties

0 **Angle of Incidence (°):**

≥2.0 **Optical Density OD (Average):**

800.00 ±16 **Cut-Off Wavelength (nm):**

**Substrate:**   
BOROFLOAT®

Hard Coated **Coating:**

850 - 1050 **Rejection Wavelength (nm):**

60-40 **Surface Quality:**

≥85 **Transmission (%):**

410 - 765 **Transmission Wavelength (nm):**

410 - 1050 **Wavelength Range (nm):**

## Environmental & Durability Factors

**Environmental Durability:**  
ML-STD-810F, Section 507.4

## Regulatory Compliance

**RoHS 2015:**  
Compliant

**Certificate of Conformance:**  
View

**Reach 253:**  
Compliant

**Country of Origin:**  
United States

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Sharp Cut-Off Wavelength
- ≥85% Transmission and OD 2.0 Blocking
- 6mm Square or 12.5/25mm Diameter Sizes
- **TECHSPEC® OD 4.0 Shortpass Filters** Also Available

OD 2.0 Shortpass Filters are cost-effective filters that provide high transmission across their transmission band and OD 2.0 blocking across their rejection band. These shortpass filters are available with cut-off wavelengths covering the visible and near-infrared spectra from 400 to 950nm. By combining these filters with our OD 2.0 Longpass Filters, custom bandpass filters can be created to meet specific application requirements. OD 2.0 Shortpass Filters are ideal for fluorescence and spectral order separation applications, with the 6 x 6mm sized filters being suited for integration into optical instrumentation. The back surface of each filter is coated with an antireflection (AR) coating, increasing the overall throughput of the filter.

## Technical Information



## Compatible Mounts