


[See all 52 Products in Family](#)

**TECHSPEC® 875nm 25mm Diameter, OD 2.0 Longpass Filter**



OD 2.0 Longpass Filters

Stock **#64-684** **20+ In Stock**

⊖ 1 ⊕ ₹10,588

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹10,588 each
Qty 6-25	₹8,999 each
Qty 26-49	₹8,470 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Longpass Filter **Type:**

**Physical & Mechanical Properties**

25.00 +0.00/-0.20 **Diameter (mm):**

3.00 ±0.1 **Thickness (mm):**

80

Clear Aperture (%):

## Optical Properties

0  
Angle of Incidence (°):

≥2.0  
Optical Density OD (Average):

875.00  
Cut-On Wavelength (nm):

Fused Silica (Corning 7980)  
Substrate: □

Traditional Coated  
Coating:

660 - 830  
Rejection Wavelength (nm):

40-20  
Surface Quality:

>85  
Transmission (%):

910 - 2000  
Transmission Wavelength (nm):

λ/4  
Transmitted Wavefront, P-V:

±2  
Cut-On Tolerance (%):

3.00  
Slope Factor (%):

Surface 1: Multi-Layer Dielectric  
Surface 2: MgF<sub>2</sub>  
Coating Specification:

660 - 2000  
Wavelength Range (nm):

## Regulatory Compliance

Compliant  
RoHS 2015:

Compliant  
Reach 224:

View  
Certificate of Conformance:

United States  
Country of Origin:

Edmund Optics India Private Limited  
Imported By:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).






## Product Details

- Sharp Cut-On Wavelength
- High Rejection/Transmission Efficiency
- Precision Fused Silica Substrate
- Variety of [OD 2.0 Longpass Filter Kits](#) are Available

TECHSPEC® OD 2.0 Longpass Filters are designed to have a sharp transition from reflection to transmission, making them ideal for various applications. Available in a variety of cut-on wavelengths, these filters are designed for fluorescence and order sorting applications. These filters feature precision fused silica substrate and high rejection/transmission efficiency. TECHSPEC® OD 2.0 Longpass Filters have a single-layer AR coating on the back surface that enhances the overall efficiency of each filter. Eliminate stray light by creating custom bandpass filters when combined with [TECHSPEC® OD 2.0 Shortpass Filters](#). A single layer AR coating on the back surface enhances the overall efficiency of each filter.

**Note:** Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact [kits@edmundoptics.com](mailto:kits@edmundoptics.com).

## Technical Information



## Compatible Mounts