

[See all 6 Products in Family](#)

## 9.0 - 36.0mm FL, CS-Mount, P-Iris, IR Cut, Telephoto Lens



Motorized Telephoto Varifocal Lenses

Stock #22-822 **1 In Stock**

1  MRP ₹53,555

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹53,555 each
Need More?	<a href="#">Request Quote</a>

Note: This item requires accessories for use | [Learn More](#)

### Product Downloads

#### General

Varifocal Lens **Type:**

#### Physical & Mechanical Properties

Motorized **Iris Option:**

62.50 **Length (mm):**

54.00 **Maximum Diameter (mm):**

68.00 **Weight (g):**

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
39° - 10°

9.0-36.0 **Focal Length Range (mm):**

2500 - ∞ **Working Distance (mm):**

f/1.5 - Closed **Aperture (f/#):**

VIS **Lens Wavelength Range:**

## Sensor

1/2.3" **Maximum Sensor Format:**

## Threading & Mounting

CS-Mount **Mount:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

Indonesia **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- 9-36mm Focal Length Range with Fields of View Between 10 and 39°
- NIR Corrected for Multi-Spectral and Day/Night Applications
- Manual, P-Iris and DC Auto-Iris Models Available

Motorized Telephoto Varifocal Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing the user to zoom in on an area of interest or zoom out for full scene investigation. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination. This IR correction will keep the image sharp in daylight, at night, or when there is a mix of visible and IR illumination. Motorized Telephoto Varifocal Lenses allow the user to optimize the field of view with 4X optical zoom capability to target an area of interest, then digitally zoom in up to 16X and are ideal for applications including Intelligent Traffic (ITS), remote sensing, security, and robotics.

**Note:** P-iris and DC auto-iris lenses are not compatible with standard machine vision cameras as they require a compatible auto-iris connector.