

[See all 3 Products in Family](#)

92 x 81mm Aperture, Acktar Blackened Laser Beam Block

See More by [Acktar](#)



Acktar Blackened Laser Beam Block



Stock #13-517 **20+ In Stock**

MRP ₹41,949

! Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-2	₹41,949 each
Qty 3+	₹39,496 each
Need More?	Request Quote

Product Downloads

General

Type:
Laser Beam Block

Model Number:
LBD-F-81

Note:

Backside has M3 screw holes for 92mm cooling fan attachment (not included)

Physical & Mechanical Properties

Black Anodized Aluminum **Construction:**

92 x 81mm **Aperture Size:**

92 L x 92 W x 10 T **Dimensions (mm):**

Optical Properties

Vacuum Black **Coating:**

100 - 10000 **Wavelength Range (nm):**

Electrical

20 **Maximum Incident Power Density (W/cm²):**

50 **Maximum Power (W):**

Threading & Mounting

M6 x 1.0 **Mounting Threads:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Israel **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Coated for High Absorbance of Laser Light
- Tubular Beam Trap or Thin, Flat Beam Block Designs
- M6 Tapped Hole for Easy Post Mounting

Acktar Blackened Laser Beam Traps and Blocks feature proprietary coatings designed to absorb incident laser light from the ultraviolet (UV) to the long-wave infrared (LWIR) spectrums. These Acktar coatings can achieve a reflectivity factor of less than 10^{-6} (beam trap designs) and have laser damage thresholds up to 20 W/cm². An M6 tapped hole on both the beam trap and beam block designs allows for easy mounting to optical posts for integration into optical systems. Acktar Blackened Laser Beam Traps and Blocks are available in multiple sizes to accommodate small or large laser beams, increasing overall lab safety by reducing the risk of laser damage. The Flat Beam Block design features back screws for a 92mm cooling fan attachment, allowing for multiple blocks to be coupled to cover large areas.