


[See all 3 Products in Family](#)

**TECHSPEC® 920nm Laser Line Mirror, 45° AOI, 12.7mm Dia., 6.35mm Thick**



920nm Laser Line Mirrors

Stock **#27-557** [CONTACT US](#)

1   MRP ₹14,630

**Price inclusive of all taxes**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹14,630 each                  |
| Qty 6-25       | ₹11,703 each                  |
| Qty 26-49      | ₹10,973 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

6.35 ± 0.20 **Thickness (mm):**

**Diameter (mm):**

12.70 +0.00/-0.10

90 **Clear Aperture (%)**

Commercial Polish **Back Surface:**

<3 **Parallelism (arcmin):**

## Optical Properties

Fused Silica (Corning 7980) **Substrate:** □

10-5 **Surface Quality:**

Laser Mirror (905-935nm) **Coating:**

905 - 935 **Wavelength Range (nm):**

M10 **Surface Flatness (P-V):**

**Coating Specification:**  
R<sub>abs</sub> 99.90% @ 920nm @ 45° AOI  
R<sub>avg</sub> 99.6% @ 820 - 1020nm @ 45° AOI

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- >99.8% Absolute Reflectivity at 920nm
- 99.5% Average Reflectivity in the 905 - 935nm Range
- High Laser Damage Threshold
- Wide Range of Laser Line Mirrors Options Available

TECHSPEC® 920nm Laser Line Mirrors are designed with an absolute reflectivity of >99.8% at 920nm at a 45° angle of incidence. These mirrors are manufactured from high quality fused silica and are designed for use with high power laser sources. Available in standard 12.7, 25.4, and 50.8mm sizes, these mirrors can be easily integrated into existing laser systems. TECHSPEC® 920nm Laser Line Mirrors feature M10 surface flatness and 10-5 surface quality to ensure reduced scattering in sensitive laser applications. These mirrors are ideal for applications including two-photon (2P) microscopy, medical imaging, and material processing.