

[See all 52 Products in Family](#)

**TECHSPEC® 925nm 25mm Diameter, OD 2.0 Longpass Filter**



OD 2.0 Longpass Filters

Stock #64-685 **CLEARANCE** 14 In Stock

- 1 + MRP ₹13,116

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹13,116 each
Qty 6-25	₹11,199 each
Qty 26-49	₹10,493 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Longpass Filter **Type:**

**Physical & Mechanical Properties**

25.00 +0.00/-0.20 **Diameter (mm):**

**Thickness (mm):**

3.00 ±0.1

80 **Clear Aperture (%)**

## Optical Properties

0 **Angle of Incidence (°)**

≥2.0 **Optical Density OD (Average)**

925.00 **Cut-On Wavelength (nm)**

**Substrate:**   
Fused Silica (Corning 7980)

Traditional Coated **Coating:**

700 - 880 **Rejection Wavelength (nm)**

40-20 **Surface Quality:**

>85 **Transmission (%)**

960 - 2000 **Transmission Wavelength (nm)**

λ/4 **Transmitted Wavefront, P-V:**

±2 **Cut-On Tolerance (%)**

3.00 **Slope Factor (%)**

**Coating Specification:**  
Surface 1: Multi-Layer Dielectric  
Surface 2: MgF<sub>2</sub>

700 - 2000 **Wavelength Range (nm)**

## Regulatory Compliance

**RoHS 2015:**  
Compliant

**Reach 224:**  
Compliant

**Certificate of Conformance:**  
[View](#)

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Sharp Cut-On Wavelength
- High Rejection/Transmission Efficiency
- Precision Fused Silica Substrate
- Variety of [OD 2.0 Longpass Filter Kits](#) are Available

TECHSPEC® OD 2.0 Longpass Filters are designed to have a sharp transition from reflection to transmission, making them ideal for various applications. Available in a variety of cut-on wavelengths, these filters are designed for fluorescence and order sorting applications. These filters feature precision fused silica substrate and high rejection/transmission efficiency. TECHSPEC® OD 2.0 Longpass Filters have a single-layer AR coating on the back surface that enhances the overall efficiency of each filter. Eliminate stray light by creating custom bandpass filters when combined with [TECHSPEC® OD 2.0 Shortpass Filters](#). A single layer AR coating on the back surface enhances the overall efficiency of each filter.

**Note:** Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact [kits@edmundoptics.com](mailto:kits@edmundoptics.com).

## Technical Information



## Compatible Mounts