

[See all 45 Products in Family](#)

Allied Vision Alvium G5-811m, 2/3" 8.1MP C-Mount, 5GigE PoE Monochrome Camera

See More by [Allied Vision](#)



Stock #23-629 [CONTACT US](#)

⊖ 1 ⊕ ₹1,42,000

ADD TO CART

Volume Pricing

Qty 1+	₹1,42,000 each
Need More?	Request Quote

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

Alvium G5-811m **Model Number:**

Allied Vision **Manufacturer:**

Alvium G5 Camera Series:

Physical & Mechanical Properties

60 × 29 × 29 Dimensions (mm):
100 Weight (g):

Full Housing:

Sensor

512KB Image Buffer:

2/3" Sensor Format:

8.10 Resolution (Megapixels):

59.00 Frame Rate (fps):

2,848 x 2,848 Pixels (H x V):

2.74 x 2.74 Pixel Size, H x V (µm):

7.80 x 7.80 Sensing Area, H x V (mm):

Sony IMX546 Imaging Sensor:

Progressive Scan CMOS Type of Sensor:

Global Shutter Type:

8/10/12 Bit Pixel Depth:

14 µs to 10 s Exposure Time:

Not Specified Dynamic Range (dB):

GigE Vision V2.2, GenICam V2.0 Machine Vision Standard:

Electrical

External power: 6.5 W at 12 VDC | Power over Ethernet: 7.1 W Power Consumption (W):

Hardware & Interface Connectivity

5GigE (PoE) Interface:

5GigE, RJ45 with Screw Locks Connector:

PoE, 12 to 24 VDC via GPIO, or with external power supply #23-581 Power Supply:

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated GPIOs GPIOs:

Hardware Trigger (GPIO) or Software Trigger Synchronization:

Back Panel Interface Port Orientation:

10-pin TFM GPIO Connector Type:

Threading & Mounting

C-Mount Mount:

1/4"-20 and M6 with Tripod Mount Adapter #14-156 Mounting Threads:

Environmental & Durability Factors

+5 to +60 Operating Temperature (°C):

-20 to +85 Storage Temperature (°C):

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)

Country of Origin:
Germany

Imported By:
Edmund Optics India Private Limited

Product Details

- 4.2 Times More Bandwidth than GigE
- Up to 24.6MP Resolution with Framrates up to 691 FPS
- Onboard Image Processing and Expansive Feature Sets

Allied Vision Alvium G5 5GigE PoE Cameras feature a lightweight, compact form factor and combines the advantages of the established 5GigE Vision standard with the flexibility of the Alvium platform. Powered by ALVUM® Technology, the sugar cube style camera delivers high image quality at a low power consumption. These cameras feature the latest industrial standard hardware and can easily be integrated into any USB3 Vision or GigE Vision system while ensuring long-term availability and reliability. With precision sensor alignment, enhanced cleanliness, fixed pattern noise correction, and defect pixel correction, resolutions up to 24.6MP and framerates up to 691 FPS are available. Allied Vision Alvium G5 5GigE PoE Cameras feature a gigabit ethernet port on the back panel and are available in a variety of monochrome and color options with either C-Mount or S-Mount lens interfaces all in the compact sugar cube format.