

[See all 5 Products in Family](#)

## Amber Glass One-Touch 4 oz. Pump-Top Dispenser



#36-298 - Amber Glass One-Touch 4 oz. Pump-Top Dispenser

Stock **#36-298** **20+ In Stock**

1  MRP ₹4,354

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹4,354 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

One-Touch®, Amber Glass Bottle **Type:**

4.00 **Size (oz):**

### Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States

**Country of Origin:**

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

---

## Product Details

- Precision Dispensing Mechanism
- Ideal for Cleaning Solutions
- Several Sizes and Bottle Options

Menda® Pump-Top Dispensers need only a simple, light touch on the dish top to dispense strictly the required amount of fluid. There is no stopper or cap to remove or need to touch the bottle. Pump-top dispensers have patented "one-handed" operation to free operator's hands, precision machined valves for smooth operation, no silicone or latex for ultra clean environments, and cam-lock hinge to keep lid open and closed and reduce orders. Menda® Pump-Top Dispensers are fabricated from 100% stainless steel and made in the USA. Pure-Take® style pump also has a patented purity protector to stop fluid from re-entering the bottle and a locking feature that will not leak when engaged, making it ideal for fluids applied with brushes and swabs. Take-Along® style pump has all the same features as Pure-Take®, but to eliminate loss from evaporation and spills it does not include a purity protector. One-Touch® style pump eliminates spraying and splashing and is perfect for cleaning with cotton balls, pads, and brushes.

**Natural HDPE Bottle:** High Density Polyethylene, suitable for many solvents. Translucent, white finish allows easy viewing of contents. Stable square shape and wide opening makes it easy to fill.

**Blue Dissipative ESD Protective Bottle:** Permanently dissipative bottles by R&R Lotion® protect static sensitive printed circuitry, low tribocharging will not easily produce a charge when moved or lifted, and stable square shape. Resistance Point to Point (RTT):  $10^9$ - $10^{10}\Omega$ .

**Amber Glass Bottle:** Dark glass bottle protects light and plastic sensitive fluids, and still translucent to allow for easy viewing of content level.

**Compatible Cleaning Solutions:** [Purosol™ Optical Cleaner](#), [Purosol™ Sport/Marine Cleaner](#), and [Red First Contact™ Cleaning Solution](#).

Note: Avoid using cleaning solutions with sodium as they may cause stainless steel to rust.

---