

[See all 69 Products in Family](#)

Basler ace acA1300-60gc Color GigE Camera, CS Mount

See More by [Basler](#)



Basler ace GigE Cameras



Stock #74-903 **1 In Stock**

MRP ₹59,472

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹59,472 each
Need More?	Request Quote

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

acA1300-60gc **Model Number:**

Basler
ace

Manufacturer:
Camera Series:

Physical & Mechanical Properties

42 mm x 29 mm x 29 mm
90

Dimensions (mm):
Weight (g):

Full

Housing:

Sensor

1/1.8"

Sensor Format:

1.30

Resolution (Megapixels):

60.00

Frame Rate (fps):

1,280 x 1,024

Pixels (H x V):

5.3 x 5.3

Pixel Size, H x V (µm):

6.8 x 5.4

Sensing Area, H x V (mm):

e2v EV76C560

Imaging Sensor:

Progressive Scan CMOS

Type of Sensor:

Global and Rolling

Shutter Type:

12 bit

Pixel Depth:

Freely programmable

Exposure Time:

51.7 dB

Dynamic Range (dB):

GigE Vision, GenICam

Machine Vision Standard:

Electrical

2.6 W

Power Consumption (W):

Hardware & Interface Connectivity

GigE

Interface:

GigE, RJ45 with Screw Locks

Connector:

PoE or 12 VDC

Power Supply:

1 opto-coupled input line, 2 general purpose I/O (GPIO) lines

GPIOs:

Hardware Trigger (GPIO), Ethernet connection, or Free Run

Synchronization:

Back Panel

Interface Port Orientation:

M8 6-pin

GPIO Connector Type:

Threading & Mounting

CS-Mount

Mount:

¼-20 with Tripod Mount Adapter [#88-517](#)

Mounting Threads:

Environmental & Durability Factors

0 °C - 50 °C

Operating Temperature (°C):

Regulatory Compliance

Exempt

RoHS 2015:

Reach 253:

[Contains SVHC\(s\)](#)

Country of Origin:

Germany

Imported By:


Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Perfect Analog Replacement
- Ultra-Small Form Factor
- Power Over Ethernet (PoE)
- Includes Basler Pylon Driver

Basler ace GigE Cameras are economical Gigabit Ethernet cameras that provide an ideal upgrade opportunity for analog camera users. With a small form factor matching that of many analog cameras (29 x 29mm), the ace can be a drop-in replacement to an existing analog system or a great choice to start a new project. Basler ace GigE Cameras can use Power Over Ethernet (PoE) (2 GigE cables required). The cameras can have long cable lengths and are the optimal choice for use on a factory floor. All cameras include the industry-proven Basler Pylon SDK Software and Driver.

Technical Information



MT9P031 Sensor QE Curve