

[See all 69 Products in Family](#)

Basler ace acA1300-60gmNIR NIR GigE Camera, CS Mount

See More by [Basler](#)



Basler ace GigE Cameras



Stock **#74-904** NEW [CONTACT US](#)

-

1

+

₹92,907

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹92,907 each
Need More?	Request Quote

Product Downloads

NIR		Spectrum:
General		
NIR Camera		Type:
acA1300-60gmNIR		Model Number:

Basler	Manufacturer:
ace	Camera Series:
Physical & Mechanical Properties	
42 mm x29 mm x29 mm	Dimensions (mm):
90	Weight (g):
Full	Housing:
Sensor	
1/1.8"	Sensor Format:
1.30	Resolution (Megapixels):
60.00	Frame Rate (fps):
1,280 x 1,024	Pixels (H x V):
5.3 x 5.3	Pixel Size, H x V (µm):
6.8 x 5.4	Sensing Area, H x V (mm):
e2v EV76C661	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global and Rolling	Shutter Type:
12 bit	Pixel Depth:
Freely programmable	Exposure Time:
50.1 dB	Dynamic Range (dB):
GigE Vision, GenICam	Machine Vision Standard:
Electrical	
2.6 W	Power Consumption (W):
Hardware & Interface Connectivity	
GigE	Interface:
GigE, RJ45 with Screw Locks	Connector:
PoE or 12 VDC	Power Supply:
1 opto-coupled input line, 2 general purpose I/O (GPIO) lines	GPIOs:
Hardware Trigger (GPIO), Ethernet connection, or Free Run	Synchronization:
Back Panel	Interface Port Orientation:
M8 6-pin	GPIO Connector Type:
Threading & Mounting	
CS-Mount	Mount:
¼-20 with Tripod Mount Adapter #88-517	Mounting Threads:
Environmental & Durability Factors	
0 °C - 50 °C	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:


	Country of Origin:
Germany	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Perfect Analog Replacement
- Ultra-Small Form Factor
- Power Over Ethernet (PoE)
- Includes Basler Pylon Driver

Basler ace GigE Cameras are economical Gigabit Ethernet cameras that provide an ideal upgrade opportunity for analog camera users. With a small form factor matching that of many analog cameras (29 x 29mm), the ace can be a drop-in replacement to an existing analog system or a great choice to start a new project. Basler ace GigE Cameras can use Power Over Ethernet (PoE) (2 GigE cables required). The cameras can have long cable lengths and are the optimal choice for use on a factory floor. All cameras include the industry-proven Basler Pylon SDK Software and Driver.

Technical Information



MT9P031 Sensor QE Curve