

BladeCam2-XGR UV Beam Profiler



Stock #91-111 NEW **1 In Stock**

MRP ₹5,81,976

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹5,81,976 each
Need More?	Request Quote

Product Downloads

General

S-BCR-XHR-UV Model Number:

Physical & Mechanical Properties

46 x 46 x 12.8 Dimensions (mm):

±1µm Dimensional Accuracy:

Optical Properties

355 - 1100 **Spectral Range:**

32 (10 Pixels) **Beam Diameter (µm):**

Sensor

3.2 x 3.2 **Pixel Size, H x V (µm):**

2,048 x 1,536 **Pixels (H x V):**

6.5 x 4.9 **Sensing Area, H x V (mm):**

1/2" **Sensor Format:**

>6 **Frame Rate:**

Electrical

1,000:1 **Signal to Noise S/N Ratio (dB):**

30 dB optical / 60 dB electrical **Peak Noise (nW/cm²):**

Threading & Mounting

Mount:
6-32 holes aligned with sensor center. 4-40 holes on camera rear. NOTE: DataRay will ship new units with a 1/4"-20 adapter

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Designed for Use from 355 to 16000nm
- Compatible with Beam Diameters Down to 52µm
- Robust and Easy to Use Free Software [Provided](#)
- Measure Beam Wander, M², Divergence, and More

DataRay Camera Beam Profilers provide excellent solutions for beam analysis of both continuous wave and pulsed laser sources. Each beam profiler features an integrated CMOS sensor (IR profilers feature Microbolometer sensors) that eliminates comet trailing for higher resolution output and allows for update rates of 60+ Hz. Sensors are available with active sizes of 6.6, 11.3, and 25mm horizontals, enabling measurement of large beam diameters. DataRay Camera Beam Profilers have the added advantage of a free, robust software with analysis features such as M² measurement, beam wander and logging, and instrument alignment. These profilers are USB3.0/2.0 powered and include a 3m flexible screw locking cable. Neutral density filters with optical densities of 1.0, 2.0, and 4.0 are included.