

[See all 7 Products in Family](#)

## BWA-CAM Adapter Plate for 12MP Camera



Stock #86-903 **NEW** [CONTACT US](#)

⊖ 1 ⊕ MRP ₹46,091

● Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹46,091 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

---

BWA-ADP-R6112-EO

**Model Number:**

## Physical & Mechanical Properties

81.0 x 78.0 x 12.4

**Dimensions (mm):**

## Regulatory Compliance

[View](#)

**Certificate of Conformance:**

United States

**Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Real-Time Analysis of Laser Beam Caustic, M<sup>2</sup>, Centroid, Ellipticity, and Astigmatism
- Compatible with CW and Pulsed Lasers with Single-Pulse Capability
- Ideal for Laser Development, Quality Control, and Optical System Monitoring
- Complies with ISO 11146 and ISO 13694

Haas Laser Technologies BWA-CAM M<sup>2</sup> Analyzer Cameras offer real-time M<sup>2</sup> measurement for continuous wave and pulsed lasers in UV, VIS, or IR wavelength configurations. Featuring a simple "one-button" calibration, this system is capable of delivering M<sup>2</sup> measurements from a single pulse, making it ideal for dynamic or single-shot laser systems. Engineered in compliance with ISO 11146 and ISO 13694 standards, the BWA-CAM provides precise evaluation of critical spatial beam parameters, including M<sup>2</sup>, beam profile, centroid, ellipticity, and astigmatism. Haas Laser Technologies BWA-CAM M<sup>2</sup> Analyzer Cameras enable users to detect optical system degradation early and optimize laser performance for maximum quality and process stability. The modular design of the BWA-CAM supports a broad range of laser wavelengths and application environments, while its high measurement accuracy and real-time data acquisition make it an essential tool for R&D, manufacturing, and laser system diagnostics.

---