

## BWA-CAM NIR Multi Spot Beam Profiler and M2 Measurement



Stock #86-926 **NEW** 1 In Stock

⊖ 1 ⊕ MRP ₹20,90,016

● Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹20,90,016 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Model Number:  
BWA-CAM-700-1200-R6-I12-EO

## Physical & Mechanical Properties

Dimensions (mm):  
123.2 x 91.1 x 78.0

## Optical Properties

Spectral Range:  
700 - 1200

Maximum Focused Beam Size ( $\mu\text{m}$ ):  
70

Minimum Focused Spot Size ( $\mu\text{m}$ ):  
28

## Sensor

Pixel Size, H x V ( $\mu\text{m}$ ):  
2.74 x 2.74

Pixels (H x V):  
4,128 x 3,008

Sensing Area, H x V (mm):  
11.31 x 8.24

Sensor Format:  
1/1.1"

Frame Rate:  
10

Shutter Type:  
Global

## Electrical

Trigger:  
Auto or External (8-pin Hirose connector HR25-7TR-8PA(73)) - [#86-758](#)

Power Consumption (V):  
1.9 - 4.0

## Hardware & Interface Connectivity

Connector:  
GigE POE

Power Supply:  
Power Supply Required and Sold Separately.  
Power Over Ethernet (PoE) Single Port injector - [#68-469](#) AND 2X of any of the following - [#63-863](#), [#63-864](#), [#59-231](#), [#59-232](#), [#59-233](#), [#59-234](#)

## Environmental & Durability Factors

Operating Temperature ( $^{\circ}\text{C}$ ):  
+0 to +55

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

Country of Origin:  
United States

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Real-Time Analysis of Laser Beam Caustic, M<sup>2</sup>, Centroid, Ellipticity, and Astigmatism
- Compatible with CW and Pulsed Lasers with Single-Pulse Capability
- Ideal for Laser Development, Quality Control, and Optical System Monitoring
- Complies with ISO 11146 and ISO 13694

Haas Laser Technologies BWA-CAM M<sup>2</sup> Analyzer Cameras offer real-time M<sup>2</sup> measurement for continuous wave and pulsed lasers in UV, VIS, or IR wavelength configurations. Featuring a simple "one-button" calibration, this system is capable of delivering M<sup>2</sup> measurements from a single pulse, making it ideal for dynamic or single-shot laser systems. Engineered in compliance with ISO 11146 and ISO 13694 standards, the BWA-CAM provides precise evaluation of critical spatial beam parameters, including M<sup>2</sup>, beam profile, centroid, ellipticity, and astigmatism. Haas Laser Technologies BWA-CAM M<sup>2</sup> Analyzer Cameras enable users to detect optical system degradation early and optimize laser performance for maximum quality and process stability. The modular design of the BWA-CAM supports a broad range of laser wavelengths and application environments, while its high measurement accuracy and real-time data acquisition make it an essential tool for R&D, manufacturing, and laser system diagnostics.