

TECHSPEC® C-Mount Adapter for 12 Position Filter Wheel and Assembly



#58-184: C-Mount Adapter for 12 Position Filter Wheel and Assembly

Stock **#58-184** **15 In Stock**

1 MRP ₹6,608

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹6,608 each
Qty 10-25	₹5,862 each
Qty 26-49	₹5,437 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

32.00 **Diameter (mm):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91-80-6845 0000

Product Details


- Holds Six or Twelve Filters
- Accepts 1" / 25mm or 1/2" / 12.5mm Diameters
- 12 Index Positions for Precise Movement

Our filter wheels offer the flexibility of using up to six (1" or 25mm) or twelve (1/2" or 12.5mm) different filters and the ability to quickly and accurately switch between them. The wheel assembly has detents in 30° increments so that it can be clicked into 12 fixed positions to allow for either horizontal or vertical alignment. The filter wheel is designed so that two wheel assemblies can be positioned face-to-face on a breadboard with less than 20mm separation.

Retainer rings are included with the filter wheels, which can hold a maximum filter thickness of 3.6mm. The C-Mount Adapters allow the use of [C-Mount components](#), including our C-Mount Lens Mounts which can hold filters of varying size and thickness. The filter wheel assembly can be easily mounted using the 1/4-20 tapped hole at the base. Other useful features include labeled filter positions, a finger groove on the outer diameter for easy rotation, and a removable front knob for interchanging filter wheels. Filter Wheel Only ([#56-783](#) & [#58-183](#)) can be purchased separately for switching wheels on the assembly, without removing filters. Common applications include fluorescence imaging, DNA sequencing, polymerase chain reaction (PCR) diagnostic instruments, attenuating low power lasers, and variable filters for machine vision. Filter Wheels are available [Pre-Loaded](#) with our TECHSPEC® Neutral Density Filters, Shortpass Filters, Longpass Filters or Bandpass Filters.

Technical Information

6-Position Filter Wheel Assembly



12-Position Filter Wheel Assembly

