


# SM Controller Cable, 5m

See More by [CCS](#)

## FCB series



Control  
Unit side

Light Unit  
side

Stock #19-971 **3 In Stock**

1  MRP ₹5,257

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹5,257 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

FCB-5 **Model Number:**

CCS **Manufacturer:**

### Physical & Mechanical Properties

5 **Length (m):**

### Hardware & Interface Connectivity

## Regulatory Compliance

[View](#)

Certificate of Conformance:

Japan

Country of Origin:

Imported By:

Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91- 80-6845 0000

## Product Details

- Ideal for Alignment and Measurement Applications
- L-Type and Cylindrical Housing Options
- Available with 8mm or 12mm Tip

CCS LED Spot Light Illuminators provide high intensity output and uniform spot lighting in a lightweight and compact housing. Available in two configurations, the L-Type orients the LED at a right angle to save horizontal space in compact applications while the cylindrical type provides a higher output intensity in a longer overall housing. Both housing options are available with red, white, blue, green, and IR outputs. CCS LED Spot Light Illuminators are ideal for alignment of LCD's or circuit boards (PCB's), dimension measurement applications, or as a light source for spot illumination. 8mm diameter tip configurations integrate directly with [TECHSPEC® CompactTL™ Telecentric Lenses](#).

### 3D-Printable Mount Files




Spot Light Configuration


[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to ¼-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.

 Application Note

Illumination Mounts for Machine Vision Applications  
[Read](#) 



Assembly of 3D Printed Mounts for Common Illumination Geometries  
[Watch](#) 

---