

DALSA Genie Nano Cable Kit

See More by [Teledyne DALSA](#)



Dalsa Genie Nano Cable Kit, #34-967



Stock **#34-967** [CONTACT US](#)

⊖ 1 ⊕ MRP ₹19,541

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹19,541 each
Need More?	Request Quote

Product Downloads

General

Camera Accessory **Type:**

Contents of Kit:
12V Power Supply, 2m GigE Cable, and 2m Breakout Cable

Included in Kit **Note:**

- 12V Power Supply with Genie Nano Aux Connector (Samtec 10-pin), 4m
- RJ-45 Ethernet Cable, 2m
- GPIO Cable, Genie Nano Aux (Samtec 10-pin) to breakout Euroblock Connector, 2m

Regulatory Compliance

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne
Authorized
Distributor

Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

Note: Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.