

[See all 34 Products in Family](#)

DALSA Genie Nano Cable Kit

See More by [Teledyne DALSA](#)



Dalsa Genie Nano Cable Kit, #34-967



Stock **#34-967** [CONTACT US](#)

-

1

+

₹16,008

ADD TO CART

Volume Pricing	
Qty 1+	₹16,008 each
Need More?	Request Quote

Product Downloads

General	
Camera Accessory	Type:
Contents of Kit: 12V Power Supply, 2m GigE Cable, and 2m Breakout Cable	

Note:	
Included in Kit: · 12V Power Supply with Genie Nano Aux Connector	

(Samtec 10-pin), 4m
· RJ-45 Ethernet Cable, 2m
· GPIO Cable, Genie Nano Aux (Samtec 10-pin) to breakout Euroblock Connector, 2m

Regulatory Compliance

Compliant	REACH 201:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

Note: Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.