

[See all 8 Products in Family](#)

TECHSPEC® Cobalt Series High Mag Kit, C Mount



SilverTL™ Telecentric Lenses



Stock #73-083 [CONTACT US](#)

- 1 + MRP ₹6,97,810

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹6,97,810 each
Need More?	Request Quote

Product Downloads

General

Contents of Kit:

- [88-603](#)
- [15-872](#)
- [62-901](#)
- [89-721](#)
- [63-233](#)
- [56-025](#)

Included Focal Lengths or Magnifications:

0.55, 0.69, 0.9

Optical Properties

0.55, 0.69, 0.9 **Included F#:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

China **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Easy to Order Kits of Our Best Selling Telecentric Imaging Lenses
- Various Magnification and Working Distance Kits Available
- TECHSPEC [SilverTL](#), [VariMagTL](#), and [CompactTL](#)

TECHSPEC® Telecentric Imaging Lens Kits provide sets of TECHSPEC® [SilverTL](#), [VariMagTL](#), and [CompactTL](#) Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring telecentric lenses including machine vision, metrology, automotive and electronic inspection, measurement, and gauging. TECHSPEC® Telecentric Imaging Lens Kits offer various selections of magnifications and working distances within the product lines. The TECHSPEC® [SilverTL](#), [VariMagTL](#), and [CompactTL](#) lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- [SilverTL](#): Silver Telecentric, Metrology and Gauging
- [VariMagTL](#): Variable Magnification Telecentric, Adjustable Magnification That Can Be Locked with a Set Screw
- [CompactTL](#): Compact Telecentric, C-Mount Lenses for Machine Vision, Factory Floors, Assembly Lines