

[See all 7 Products in Family](#)

Coherent® LabMax-Pro SSIM 1268881 (Recertified 05-P)

See More by [Coherent®](#)



#35-302 Coherent® LabMax-Pro SSIM 1268881

Stock **#35-203-RCD-05P** RECERTIFIED **2 In Stock**

⊖ 1 ⊕ MRP ₹1,37,529

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹1,37,529 each
Need More?	Request Quote

Product Downloads

General

1268881 **Model Number:**

Power, Energy, and Beam Position **Type:**

±1.0 **Calibration Uncertainty (%):**

Max Repetition Rate: 20,000Hz
Coherent® [Thermopile Power Sensors, Position](#) **Note:**

Sensing Thermopile Power Sensors, Laser Energy Sensors, or High Sensitivity Sensors Sold Separately

Physical & Mechanical Properties

105.00	Length (mm):
105.00	Width (mm):
0.3	Weight (kg):
32	Depth (mm):

Optical Properties

0.1% Full Scale at 10Hz 0.2% Full Scale at 20kHz	Resolution:
---	--------------------

Electrical

0 to 1, 2, or 4 V (Selectable)	Analog Output:
625,000	Power Sampling Rate (Hz):

Hardware & Interface Connectivity

90-260 VAC, 50/60 Hz AC Power Adapter	Power Supply:
USB & RS232	Computer Interface:

Environmental & Durability Factors

+5 to +40	Operating Temperature (°C):
-20 to +70	Storage Temperature (°C):

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Coherent® [Thermopile Power Sensors](#), [Position Sensing Thermopile Sensors](#), [Laser Energy Sensors](#), or [High Sensitivity Sensors](#) Sold Separately
- FieldMate Used to Measure Laser Power
- FieldMaxI Used to Measure Laser Power and Energy
- ISO 17025 Certified

Coherent® Laser Power and Energy Meters are designed to accurately measure and help tune the power or energy of continuous wave and pulsed lasers. The FieldMate, which features an analog needle with a large LCD display, is compatible with thermopile or optical sensors and is an economical solution for measuring laser power when advanced data analysis is not necessary. The FieldMaxI utilizes a large, backlit LCD screen and features a USB interface for computer connectivity. Coherent® Laser Power and Energy Meters feature FieldMaxI-TQ, which is compatible with thermopile or optical sensors, while the FieldMaxI-TOP is compatible with thermopile, optical, or pyroelectric sensors. The LabMax is an all-in-one solution for measuring laser power or energy and is ideal for applications requiring advanced data analysis. The LabMax-TOP is compatible with thermopile, optical, or pyroelectric sensors. The LabMax Pro is the most advanced power and energy meter and is compatible with thermopile, optical, and pyroelectric sensors, as well as the PowerMax Pro high speed sensor technology. The LabMax Pro can provide advanced analysis up to 625kHz.