

Coherent® PowerMax USB PS19Q Measurement System 1168343 | 1W Max Power

See More by [Coherent®](#)



Stock #68-626 **2 In Stock**

⊖ 1 ⊕ MRP ₹2,70,810

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹2,70,810 each
Need More?	Request Quote

Product Downloads

General

Model Number:
PS19Q Coherent Part Number: 1168343

Type:
Meterless

Linearity (%):
±1

Calibration Uncertainty (%):
±2

Long Pulse Joule Mode Range (J):

0.001 - 1

Long Pulse Joule Mode Accuracy (%):

±3

Cooling Method:

Air

Response Time (s):

2

Note:

Includes a Wedged Quartz Window to Eliminate Thermal Background Radiation and Air Current Effects

Maximum Incident Energy Density:

50mJ/cm² (10ns, 1064nm)

Physical & Mechanical Properties

Active Area Diameter (mm):

19

Optical Properties

Calibration Wavelength (nm):

514

Wavelength Range (nm):

300 - 2100

Wavelength Range (µm):

0.3 - 2.1

Sensor

Type of Sensor:

Thermopile

Electrical

Spectral Compensation Accuracy (%):

±1.5

Maximum Incident Power Density (kW/cm²):

0.5

Power Range:

100µW - 1W

Minimum Power (mW):

0.1

Maximum Power (W):

1

Noise Equivalent Power:

3µW

Hardware & Interface Connectivity

Length of Cable (m):

2.5

Computer Interface:

USB

Environmental & Durability Factors

Thermally Stabilized:

Yes

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Thermopile Detector Element for High Power Measurements
- Measure Beam Position on Detector Surface
- ISO 17025 Certified

Coherent® Beam Position Sensing Thermopile Power Sensors are all-purpose sensors designed to measure the average power or energy of a wide variety of continuous wave or pulsed lasers. Coherent Beam Position Sensing

Thermopile Power Sensors utilize a quadrant thermopile detector disk to sense the position of the laser beam on the detector surface while measuring the laser power. Coherent thermopile sensors can operate across a wide range of input powers, and do not saturate.

Note: The LM-20 is designed for embedded use and must be mounted on a heat sink.

;