

Coherent® Beam Position Thermopile Power Sensors 1098320 | 100mW-45W

See More by [Coherent®](#)



Stock **#12-398** [CONTACT US](#)

-

1

+

₹1,54,350

ADD TO CART

Volume Pricing	
Qty 1+	₹1,54,350 each
Need More?	Request Quote

Product Downloads

General	
Model Number: LM45 HTD Coherent Part Number: 1098320	
Type: Meter required	
Linearity (%): ±1	
Calibration Uncertainty (%): ±2	
Long Pulse Joule Mode Range (J): 0.5 - 10	

±3	Long Pulse Joule Mode Accuracy (%):
Air	Cooling Method:
#35-203 , #12-393 , #59-978 , #88-411 , #66-277 , #88-412	Compatible Meters:
Physical & Mechanical Properties	
19	Active Area Diameter (mm):
Optical Properties	
10,600	Calibration Wavelength (nm):
0.25 - 10.6	Wavelength Range (µm):
Sensor	
Quad Element Thermopile	Type of Sensor:
Electrical	
±1.5	Spectral Compensation Accuracy (%):
45	Maximum Incident Beam Power (W):
Hardware & Interface Connectivity	
2.5	Length of Cable (m):
DB-25	Computer Interface:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Thermopile Detector Element for High Power Measurements
- Measure Beam Position on Detector Surface
- ISO 17025 Certified

Coherent® Beam Position Sensing Thermopile Power Sensors are all-purpose sensors designed to measure the average power or energy of a wide variety of continuous wave or pulsed lasers. Coherent Beam Position Sensing Thermopile Power Sensors utilize a quadrant thermopile detector disk to sense the position of the laser beam on the detector surface while measuring the laser power. Coherent thermopile sensors can operate across a wide range of input powers, and do not saturate.

Note: The LM-20 is designed for embedded use and must be mounted on a heat sink.