

[See all 3 Products in Family](#)

Coherent® High Power Water-Cooled Thermopile Sensor PM3K+ 1409627 | 3kW Max Power

See More by [Coherent®](#)



Stock #12-407 [CONTACT US](#)

1 [-](#) [+](#) MRP ₹3,88,161

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹3,88,161 each
Need More?	Request Quote

Product Downloads

General

1409627 **Model Number:**

[Meter required](#) **Type:**

3 **Calibration Uncertainty (%):**

Cooling Method:

Water

Response Time (s):

15 5s if Speed-up is on

Compatible Meters:

[#35-203](#), [#59-978](#), [#88-411](#), [#66-277](#), [#23-660](#), [#23-661](#)

Maximum Incident Energy Density:

600mJ/cm² (10ns, 1064nm)

Physical & Mechanical Properties

Active Area Diameter (mm):

50

Optical Properties

Calibration Wavelength (nm):

1070

Wavelength Range (nm):

250 - 11000

Wavelength Range (µm):

0.25 - 11

Electrical

Power Resolution (W):

1

Power Range:

5W-3kW

Maximum Power (W):

3000

Minimum Power (W):

5

Hardware & Interface Connectivity

Computer Interface:

DB-25

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Water-Cooling Capability to Withstand Laser Powers up to 5kW
- Spectrally Flat from 0.25 to 11µm
- Large 50mm Aperture for Accepting a Wide Range of Beam Diameters

Coherent® High Power Water-Cooled Thermopile Sensors are designed to withstand high power lasers up to 5kW. The water-cooling mechanism reduces the heat transferred to the sensor from input lasers to prevent sensor damage when used with the recommended minimum water flowrate. This makes these sensors ideal for use with >100W power industrial CO₂ and Nd:YAG lasers that exceed the power handling capability of standard thermopile sensors. Coherent® High Power Water-Cooled Thermopile Sensors cover a broad wavelength spectrum from 190 - 11,000nm, allowing for them to be used in most laser applications. A power resolution of 1W allows for these thermopile sensors to provide exceptional measurement accuracy of high power lasers. Refer to manual included with purchase for fitting and water flow specifications.