

[See all 15 Products in Family](#)

# Coherent® EnergyMax 1110746 | 500μJ-1000mJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#12-386** [CONTACT US](#)

MRP ₹1,86,912

**1** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,86,912 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

**Model Number:**  
 J-25MB-HE  
 Coherent Part Number: 1110746

**Type:**  
[Meter required](#)

**Linearity (%):**  
 ±3

**Calibration Uncertainty (%):**  
 ±2

Noise Equivalent Energy ( $\mu\text{J}$ ):

<16

Compatible Meters:

[#35-203](#) or [#66-277](#)

Maximum Incident Energy Density:  
500mJ/cm<sup>2</sup> (10ns, 1064nm)

Energy Range:  
500 $\mu\text{J}$  - 1J

Preferred Meter:

[#88-412](#)

## Physical & Mechanical Properties

Active Area Diameter (mm):  
25

## Optical Properties

Calibration Wavelength (nm):  
1064

Maximum Pulse Width ( $\mu\text{s}$ ):  
17

Wavelength Range (nm):  
190 - 12000

## Sensor

Type of Sensor:  
Pyroelectric

## Electrical

Maximum Repetition Rate (pps):  
1000

Maximum Incident Beam Power (W):  
5

## Hardware & Interface Connectivity

Connector:  
DB25

Length of Cable (m):  
2.5

## Regulatory Compliance

RoHS 2015:  
[Exempt](#)

Reach 224:  
[Contains SVHC\(s\)](#)

Certificate of Conformance:  
[View](#)

Country of Origin:  
United States

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.