

[See all 15 Products in Family](#)

# Coherent® EnergyMax 1110856 | 100nJ-200µJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock #12-385 **4 In Stock**

MRP ₹1,93,815

**1** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,93,815 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

**Model Number:**  
 J-10MT-10KHZ  
 Coherent Part Number: 1110856

**Type:**  
[Meter required](#)

**Linearity (%):**  
 ±3

**Calibration Uncertainty (%):**  
 ±2

Noise Equivalent Energy ( $\mu\text{J}$ ):

<10

Compatible Meters:

[#35-203](#)

Maximum Incident Energy Density:  
50mJ/cm<sup>2</sup> (10ns, 1064nm)

Energy Range:

100nJ - 200 $\mu\text{J}$

Preferred Meter:

[#88-412](#)

## Physical & Mechanical Properties

Active Area Diameter (mm):

10

## Optical Properties

Calibration Wavelength (nm):

1064

Maximum Pulse Width ( $\mu\text{s}$ ):

1.7

Wavelength Range (nm):

190 - 2100

## Sensor

Type of Sensor:

Pyroelectric

## Electrical

Maximum Repetition Rate (pps):

10000

Maximum Incident Beam Power (W):

1

## Hardware & Interface Connectivity

Connector:

DB25

Length of Cable (m):

2.5

## Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.