

[See all 45 Products in Family](#)

Coherent® OBIS™ LX/LS Laser Box with Power Supply 1228877

See More by [Coherent®](#)



Coherent® OBIS™ LX/LS Laser Box with Power Supply 1228877



Stock #33-351 **2 In Stock**

1 MRP ₹3,40,371

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹3,40,371 each
Need More?	Request Quote

Product Downloads



General

Note:
Includes Power Supply, USB Cable, and Software on USB Drive

1228877 **Model Number:**

50 **Digital Modulation Impedance (Ω):**

Physical & Mechanical Properties

Dimensions (mm):

241 x 184 x 88 (Laser Box)
189 x 89.4 x 47.1 (Power Supply)

Electrical

Analog Modulation Impedance (Ω):

2,000

Hardware & Interface Connectivity

Computer Interface:

USB 2.0, RS-232

Regulatory Compliance

RoHS 2015:

Exempt

Reach 224:

Contains SVHC(s)

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Same Compact Design for All Wavelength Options
- Integrated Control Electronics with Analog and Digital Modulation
- Circular Beam with Superior Beam Quality
- **Coherent® High Performance OBIS™ LX/LS Fiber-Pigtailed Laser Systems** Also Available

Coherent® High Performance OBIS™ LX/LS Laser Systems are compact, plug-and-play lasers that offer a wide range of wavelengths from the ultraviolet to the near-infrared in a single platform. Although each laser utilizes one of two technologies, either Coherent's proprietary Optically Pumped Semiconductor Laser (OPSL) or laser diode-based, these laser systems feature the same beam parameters in packages that allow the user to plug-and-play alternate wavelengths as needed. Coherent® High Performance OBIS™ LX/LS Laser Systems includes a USB, RS-485, and full I/O interface. A multicolor LED has been integrated into the top cover to provide laser status at a glance.

OBIS Laser System Startup Guide

This downloadable PDF provides guidance on interfacing with OBIS controllers and power supplies, mounting and connecting the heatsink, and starting modulation.

[Download Startup Guide](#)

Note: A power supply is required for operation and sold separately. OBIS remote is required for CDRH certified systems. The OBIS heat sink is recommended.

Three power supply options are available, but only one is required. **#87-472** (not CDRH certified) includes a power supply with power cord. **#87-473** (CDRH certified) includes a 1m laser-to-remote cable, and DC power supply with power cable. **#87-475** (CDRH certified) includes a 6 laser scientific remote, internal power supply, and six 1m laser-to-remote cables with power cord.

Coherent® High Performance OBIS™ LX/LS Laser Systems are designed for an extensive range of OEM or scientific applications including environmental monitoring, inspection, or machine vision, or for use in the life sciences for the fluorescence excitation of dyes and proteins in flow cytometry, microscopy, DNA sequencing, polymerase chain reaction (PCR) diagnostic instruments, or drug delivery. These lasers feature smart electronics to ensure superior low-noise optical performance, and an ultra-small controller that has been integrated into the laser head.

Technical Information

