

[See all 1 Products in Family](#)

Color Corrected F-Theta Lens, 163mm, 1030nm



Stock #26-809 **3 In Stock**

MRP ₹5,39,762

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹5,39,762 each
Need More?	Request Quote

Product Downloads

General

Col **Type:**

14mm (max input aperture diameter) **Note:**

Edmund Optics® **Manufacturer:**

Physical & Mechanical Properties

118.0 +0/-0.2 **Maximum Diameter (mm):**

1970	Weight (g):
±7.1	X/Y Mirror Angle (°):
260 @ 1030nm	Flange Distance (mm):
14	Input Beam Diameter, 1/e² (mm):
89	Maximum Length (mm):

Optical Properties

163.00	Focal Length FL (mm):
Optical Glass	Substrate: <input type="checkbox"/>
20	Scan Angle (°):
80x80	Scan Field (mm):
F-Theta Only: 6.7	Telecentricity (°):
>95	Transmission (%):
185.00 @ 1030nm (with cover glass)	Working Distance (mm):
1000 - 1060	Wavelength Range (nm):
113	Scan Field Diameter (mm):
22	Focus Size Diameter, 1/e² (µm):

Threading & Mounting

M79x1.0	Mounting Threads:
---------	--------------------------

Regulatory Compliance

View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Ideal for Broad Spectral Laser Scanning Applications
- Diffraction Limited Across the Scan Field with Low Wavefront Error
- Long Working Distance and Large Scan Area

Color Corrected F-Theta Lenses are designed for use with material processing lasers that typically have relatively large chromatic bandwidths. Similar to an achromatic lens, these F-theta lenses ensure that each wavelength across a given broadband range is focused on the same focal plane and maintains the same scanning geometry, as opposed to a standard monochromatic F-theta lens. When used with [galvanometers](#), [beam expanders](#), and [laser sources](#), these lenses provide flat fields at the image plane of scanning systems. Color Corrected F-Theta Lenses are ideal for a range of material processing and medical applications such as laser cutting, welding, drilling, confocal microscopy, and ophthalmology.