

[See all 4 Products in Family](#)

70mm, Compact Motorized Rotation Stage, Metric



70mm, Compact Motorized Rotation Stage

Stock **#23-929** **1 In Stock**

-

1

+

₹81,900

ADD TO CART

Volume Pricing	
Qty 1+	₹81,900 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
Controller Required: #23-931	Note:
Stepper Motor	Type of Motor:
Physical & Mechanical Properties	
Rotary	Type of Movement:

Ball Bearing	Guide System:
360	Travel (°):
0.03	Accuracy (°):
0.2	Backlash (°):
Aluminum, 3D Printed Plastic	Construction:
44.7	Height (mm):
0.5	Load Capacity (kg):
0.03	Repeatability (°):
240	Speed (°/s):
0.25	Weight (kg):
70	Table Diameter (mm):
0.0083	Parallelism (°):
0.02	Min. Incremental Movement (°):

Optical Properties

0.02°	Resolution (µm):
-------	------------------

Electrical

500	Maximum Operating Current (mA):
-----	---------------------------------

Hardware & Interface Connectivity

Gear Transmission	Type of Drive:
USB-C	Computer Interface:

Threading & Mounting

(4) M6 x 1.0, (4) M3 x 0.5, (8) M2 x 0.4	Mounting Threads:
--	-------------------

Environmental & Durability Factors

10-40	Operating Temperature (°C):
-------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Compact Footprint and Economic Price Point
- Light-weight Housing with Durable Stage Platform
- Compatible with [TECHSPEC Stages](#)
- Use Power Supply [#21-075](#) to Power Controller [#23-931](#)

Compact Motorized Rotation Stages are a cost-effective solution for motorized rotation adjustment within an optical system. These stages feature an anodized aluminum stage platform for precision mounting, with a preinstalled breadboard mounting plate. The compact overall footprint maximizes space efficiency to add motorization to space constrained systems. Compact Motorized Rotation Stages share the same hole patterns as our [TECHSPEC stages](#), making them an ideal lab bench component for motorized system building. Requires a Controller, [#23-931](#), which can be easily connected via an included 1m USB-C to USB-A cable.