

Complete Light Measurement System for Low Light



Stock #72-547 **1 In Stock**

⊖ 1 ⊕ ₹3,17,700

ADD TO CART

Volume Pricing	
Qty 1+	₹3,17,700 each
Need More?	Request Quote

Product Downloads

General

5 pA- 1mA current **Range:**

Physical & Mechanical Properties

5x3x6 **Dimensions (mm):**

Environmental & Durability Factors

0-40 **Operating Temperature (°C):**

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited

Product Details

- Response Time of 100 μ Seconds
- Hand-held, Compact, Ergonomic Design
- Extensive Software Included

International Light Technologies Light Meters are handheld light/lux meters that feature Accuspan software that automatically sets averaging while measuring the target light. These instruments offer excellent resolution with an exceptional response time of 100 μ Seconds, allowing for use in a variety of illumination intensity situations. Available in UV, NIR, and Broadband wavelength ranges, these light meters cover a range of wavelengths and can store up to 16 measurements per second. International Light Technologies Light Meters are available in two different models, general light measuring and low light measuring which offer different sensitivities for different light level applications. The ILT2400 has a 50pA– 1mA measurement range and the ILT2500, the low light version, has a 5pA- 1mA minimum measurement range. These light meters are NIST Certified and are ideal for photography, cinematography, architecture, and environmental science.