

[See all 3 Products in Family](#)

2.5mm CA, Corning® Varioptic® A-PE Series Variable Focus Liquid Lens Development Kit



Corning® Varioptic® A-PE Series Variable Focus Liquid Lenses



Stock **#23-230** **3 In Stock**

-

1

+

₹88,200

ADD TO CART

Volume Pricing	
Qty 1+	₹88,200 each
Need More?	Request Quote

Product Downloads

General	
Development Kit	Type:
Contents of Kit:	
Corning® Varioptic® A-PE-25HX-33 Lens	
USB-MUniversal (with 4 and 6 pin connector and USB compatibility)	
USB-B to USB-A Cable	
Focuslab Software	
Control Software Documentation Package	

A-PE-25HO-33	Model Number:
Typical Applications: Compact optical systems such as barcode readers, industrial cameras, & medical imaging and biometrics systems	
Physical & Mechanical Properties	
8.80 (packaged lens)	Diameter (mm):
2.5	Clear Aperture CA (mm):
2.80 (packaged lens)	Thickness (mm):
Optical Properties	
VIS	Coating:
-5 to +13 diopter	Focus Range (mm):
97 @587nm	Transmission (%):
30nm	Transmitted Wavefront Error, RMS:
Environmental & Durability Factors	
-30 to +85	Operating Temperature (°C):
-40 to +85	Storage Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
France	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Combine a Liquid Lens with Dedicated, Calibrated Driver Board
- Temperature Compensation and Response Time Optimization Features
- Include Control Software and Documentation Package
- [A-P Series Liquid Lenses](#) Also Available

Corning® Varioptic® A-PE & V-PE Series Variable Focus Liquid Lens Development Kits feature a variable focus liquid lens with a dedicated, calibrated driver board for enhanced performance, temperature compensation, and response time optimization, as well as all necessary cables and control software for operation. The driver board enables advanced features including temperature compensation algorithms, response time optimization for optical power changes, and sweep mode which acquires clear images while the liquid lens is still in motion. The V-PE Series expands on this technology with an 8-electrode design, enabling independent control of spheres at ±24 diopters of power, cylinders at ±5 diopters of power, and axis for astigmatism correction without any moving parts, ensuring silent, reliable operation. Corning® Varioptic® A-PE & V-PE Series Variable Focus Liquid Lenses are ideal for use in barcode readers, industrial inspection, medical imaging, and biometrics applications and are fully compatible with the [AF Explorer Camera](#) for plug-and-play operation. Also included in the development kit is a documentation package with additional application information.