

[See all 2 Products in Family](#)

Corning® Varioptic® AF Explorer Development Kit with Sony IMX335 Sensor



Stock #22-097 [CONTACT US](#)

- 1 + MRP ₹1,20,461

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹1,20,461 each
Need More?	Request Quote

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

Corning® Varioptic® **Manufacturer:**

1 x AF Explorer Camera Board **Contents of Kit:**

1 x Sony IMX335 Sensor
1 x TOF Sensor
1 x USB Type-C Cable
1 x Mounting Pedestals
White LEDs
AF Lab Camera Software

Physical & Mechanical Properties

Dimensions (mm):
110 x 70 x 5 (excludes sensor and lens mount)

Weight (g):
504

Housing:
Board Level

Sensor

Sensor Format:
1/2.8"

Resolution (Megapixels):
5.04

Frame Rate (fps):
60.00

Pixels (H x V):
2,592 x 1,944

Pixel Size, H x V (µm):
2.00 x 2.00

Sensing Area, H x V (mm):
5.18 x 3.89

Imaging Sensor:
Sony IMX335

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Rolling

Pixel Depth:
10 bit

Machine Vision Standard:
AF Explorer Software

Electrical

Power Consumption (W):
1.65W - 2.60W (LED Off/On, 5MP 30fps)

Hardware & Interface Connectivity

Interface:
USB 3.1 Gen 1

Connector:
USB 3.1 Gen 1, Type-C

Power Supply:
Power over USB

Interface Port Orientation:
Back Panel (Right Angle)

GPIO Connector Type:
N/A

Threading & Mounting

Mount:
C-Mount or S-Mount

Mounting Threads:
1/4-20 Tripod Adapter, Built-in Pedestals

Environmental & Durability Factors

Operating Temperature (°C):
0°C to +65°C

Storage Temperature (°C):
-20°C to +85°C

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
South Korea

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,


Product Details

- Ideal for Evaluating and Exploring Liquid Lens Technology
- Easily Driven via AF Lab Software over USB
- Plug-and-Play With TECHSPEC® Liquid Lens [Cx Series](#) and [M12](#) Lenses

The Corning® Varioptic® AF Explorer Autofocus Board Level Camera for Liquid Lenses provides an easy-to-use evaluation platform for exploring liquid lens technology and its benefits to machine vision applications. Featuring plug-and-play compatibility with our TECHSPEC® Liquid Lens [Cx Series](#) and [M12](#) Lenses, the AF Explorer is easily driven via the included AF Explorer software for adjusting basic sensor settings, autofocus modes, autofocus algorithms, and more. The Corning® Varioptic® AF Explorer Autofocus Board Level Camera for Liquid Lenses is ideal for those looking to incorporate liquid lens technology into their machine vision or life science application for the first time, or as a standalone camera in production applications. Included with each AF Explorer is the main electronics board, an imaging sensor, time of flight (TOF) sensor, software, and product documentation.

Note: Additional sensor boards are available for use with the AF Explorer, including the Samsung M3085 (8MP 1/3.2"), Sony IMX307 (2MP 1/2.8"), and Sony IMX219 (8MP 1/4"), all optimized for use with our TECHSPEC® Liquid Lens Imaging Lenses. Please contact us for more information.

Technical Information



The AF Lab software allows for users to acquire images, record video, and easily use auto-focus features such as switched focus between different regions of interest.
