

[See all 24 Products in Family](#)

Diffused Light Compact Spot Light HLV3-14RD-HU

See More by [CCS](#)



Stock **#21-852** **1 In Stock**

-

1

+

₹41,064

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹41,064 each
Need More?	Request Quote

Product Downloads

General	
HLV3-14RD-HU	Model Number:
LED Illuminator	Type of Illumination:
CCS	Manufacturer:
Spot Light	Geometry:
	Illumination Mode:

Constant	
Physical & Mechanical Properties	
Dimensions (mm): 14 x28 x20 (WxD xH), Tip diameter 8 mm	
Weight (g): 18	
Active Area (mm): 7	
Optical Properties	
Color: Red	
Wavelength (nm): 635	
Electrical	
Power Consumption (W): 0.7	
Maximum Input Current: 275mA	
Hardware & Interface Connectivity	
Power Supply: Power Supply & Controller Required and Sold Separately: USA: #73-491 & #21-880 Europe: #73-491 & #21-880 Japan: #89-513 & #21-880 Korea: #33-773 & #21-880 China: #73-491 & #21-880	
Regulatory Compliance	
RoHS 2015: Exempt	
Reach 224: Contains SVHC(s)	
Certificate of Conformance: View	
Country of Origin: United States	
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Ideal for Alignment and Measurement Applications
- L-Type and Cylindrical Housing Options
- Available with 8mm or 12mm Tip

CCS LED Spot Light Illuminators provide high intensity output and uniform spot lighting in a lightweight and compact housing. Available in two configurations, the L-Type orients the LED at a right angle to save horizontal space in compact applications while the cylindrical type provides a higher output intensity in a longer overall housing. Both housing options are available with red, white, blue, green, and IR outputs. CCS LED Spot Light Illuminators are ideal for alignment of LCD's or circuit boards (PCB's), dimension measurement applications, or as a light source for spot illumination. 8mm diameter tip configurations integrate directly with [TECHSPEC® CompactTL™ Telecentric Lenses](#).

3D-Printable Mount Files



Spot Light Configuration

**DOWNLOAD
NOW**

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications
[Read](#) 



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries
[Watch](#) 