

[See all 78 Products in Family](#)

Preloaded Norland Optical Adhesive NOA 61 Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA 60 shown as an example)

Stock #55-155 [CONTACT US](#)

- 1 + MRP ₹2,921

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-11	₹2,921 each
Qty 12-19	₹2,634 each
Need More?	Request Quote

Product Downloads

General	
0.1	Size (oz):
61	Norland Number:
4 months	Shelf Life:
	Type:

Barrel

Typical Applications:

Preferred adhesive for precision optical bonding.
Meets ML-A-3920. Low shrinkage and resiliency of adhesive minimizes strain

Note:

Contains 2g of adhesive

Physical & Mechanical Properties

Size (cc):

3.00

Optical Properties

Index of Refraction (n_d):

1.56 @ 589nm

Absorption Range (nm):

320 - 380

Material Properties

Glass Bonding:

Excellent

Metal Bonding:

Excellent

Plastic Bonding:

Fair

Viscosity (cps):

300

Bonding Type:

Glass to Glass/Metal

Energy for Full Cure (J/cm²):

3

Environmental & Durability Factors

Durability:

Tough

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 253:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES

Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.