

[See all 78 Products in Family](#)

Preloaded Norland Optical Adhesive NOA 61 Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA 60 shown as an example)

Stock **#55-155** 10 In Stock

-

1

+

₹2,430

ADD TO CART

Volume Pricing	
Qty 1-4	₹2,430 each
Qty 5+	₹2,331 each
Need More?	Request Quote

Product Downloads

General	
0.1	Size (oz):
61	Norland Number:
4 months	Shelf Life:
Barrel	Type:

Typical Applications: Preferred adhesive for precision optical bonding. Meets MIL-A-3920. Low shrinkage and resiliency of adhesive minimizes strain	
Note: Contains 2g of adhesive	
Physical & Mechanical Properties	
Size (cc): 3.00	
Optical Properties	
Index of Refraction (n _d): 1.56 @ 589nm	
Absorption Range (nm): 320 - 380	
Material Properties	
Glass Bonding: Excellent	
Metal Bonding: Excellent	
Plastic Bonding: Fair	
Viscosity (cps): 300	
Bonding Type: Glass to Glass/Metal	
Energy for Full Cure (J/cm²): 3	
Environmental & Durability Factors	
Durability: Tough	
Regulatory Compliance	
RoHS 2015: Compliant	
Certificate of Conformance: View	
Reach 251: Compliant	
Country of Origin: United States	
Imported By: Edmund Optics India Private Limited	

Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
 - Adhesives for Glass, Metal, and Plastic Bonding
 - Require a Dispensing Unit & Dispenser Tips for Use
 - [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available
- Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.