

[See all 78 Products in Family](#)

Preloaded Norland Optical Adhesive NOA 88 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#14-840** **4 In Stock**

MRP ₹4,195

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-11	₹4,195 each
Qty 12-19	₹3,781 each
Need More?	Request Quote

Product Downloads

General

0.34 **Size (oz):**

88 **Norland Number:**

4 months **Shelf Life:**

Type:

Barrel

Typical Applications:

Low outgassing and low viscosity for bonding glass or metal. Excellent transmission in the UV.

Note:

Contains 10g of adhesive

Optical Properties

Index of Refraction (n_d):

1.56 @ 589nm

Absorption Range (nm):

315 - 395

Material Properties

Glass Bonding:

Excellent

Metal Bonding:

Excellent

Plastic Bonding:

Fair

Viscosity (cps):

250

Bonding Type:

Glass to Glass/Metal

Energy for Full Cure (J/cm²):

5

Environmental & Durability Factors

Durability:

Hard & Flexible

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 251:

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES

Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.