

[See all 3 Products in Family](#)

# DoAll Light



Stock #75-233 **NEW** [CONTACT US](#)

- 1 + ₹6,39,015

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | ₹6,39,015 each                |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

DoAll-UR-PS-Kit **Model Number:**

LED Illuminator **Type of Illumination:**

Smart Vision Lights LLC **Manufacturer:**

**Geometry:**  
Dome Light, Low Angle Darkfield Ringlight, Mid Angle Darkfield Ringlight, RGBW Ringlight, Four Quadrant

Constant or Strobed **Illumination Mode:**

## Physical & Mechanical Properties

213.44 Dia. x 112.88 H **Dimensions (mm):**

1.58 **Weight (kg):**

## Optical Properties

RGB-IR **Color:**

0 - 750 **Working Distance (mm):**

## Electrical

15 A for both outputs combined **Output Current (A):**

## Hardware & Interface Connectivity

2 5-Pin M12 Connectors **Connector:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

## Product Details

- All-In-One Solution for Machine Vision Lighting Applications
- Combines 6 Illumination Geometries into One Multi-Functional Illuminator
- Features RGB, White and NIR Illumination

The Smart Vision Lights DoAll Light provides an all-in-one solution for machine vision lighting applications that require various wavelengths and illumination profiles. This light combines a dome, low and mid angle darkfield ring, RGBW ring, four-quadrant ring, and NIR ring light into one system. The included controller allows the user to program and save multiple illumination sequence variations for ease of use between inspections. The Smart Vision DoAll Light features RGB, white, and NIR illumination to address multiple application spaces. This versatile illuminator includes all required components for operation, including the controller, power supply, power & ethernet cables, URCap USB stick with software, and mounting hardware. The DoAll Light's compact size allows for easy integration into smaller electronic assembly inspection systems or for use in large-scale automatic and logistics applications.

| Color | Dominant Wavelength | Irradiance             | OverDrive™ Irradiance   | Illuminance | OverDrive™ Illuminance |
|-------|---------------------|------------------------|-------------------------|-------------|------------------------|
| Red   | 625 nm              | 1.4 mW/cm <sup>2</sup> | 10.6 mW/cm <sup>2</sup> | 2,469 lux   | 18,300 lux             |
| Green | 533 nm              | 1.9 mW/cm <sup>2</sup> | 9.5 mW/cm <sup>2</sup>  | 10,420 lux  | 51,900 lux             |
| Blue  | 484 nm              | 2.5 mW/cm <sup>2</sup> | 14.1 mW/cm <sup>2</sup> | 2,860 lux   | 15,900 lux             |
| White | 556 (5443 K)        | 2.8 mW/cm <sup>2</sup> | 17.6 mW/cm <sup>2</sup> | 8,960 lux   | 57,100 lux             |
| IR    | 850 nm              | 8.2 mW/cm <sup>2</sup> | 36.6 mW/cm <sup>2</sup> | N/A         | N/A                    |