

Edge Reticle for Pattern Projectors

See More by [Advanced Illumination](#)



#88-522: Edge Reticle for Pattern Projectors

Stock **#88-522** 1 In Stock

-

1

+

₹15,300

ADD TO CART

Volume Pricing	
Qty 1+	₹15,300 each
Need More?	Request Quote

Product Downloads

General

Accessory	Type of Illumination:
Advanced Illumination	Manufacturer:

Physical & Mechanical Properties

20.80	Diameter (mm):
<50	Line Thickness (µm):

1.50	Thickness (mm):
Optical Properties	
Chrome Pattern	Coating:
Float Glass	Substrate: ☐
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:
United States	Country of Origin:
Edmund Optics India Private Limited	Importer:

Product Details

Power supply and C-mount imaging lens are required and sold separately.

- Multiple Wavelength Options Available
- Equip C-Mount Imaging Lenses to Control Illumination Geometry
- Ideal for 3D Reconstruction and Mapping

Advanced Illumination LED Pattern Projectors are compact illuminators designed for applications requiring structured illumination. These illuminators can be used with any C-mount compatible imaging lens and negatively patterned 21mm reticle to achieve specific structured illumination geometries. When used without a reticle, these illuminators can be adjustable spotlights. Advanced Illumination LED Pattern Projectors are ideal for 3D reconstruction and mapping. The illuminators are available in blue, green, red or white.

Note: Power supply and C-mount imaging lens are required and sold separately.</>

Technical Information



