

TECHSPEC® Elliptical Mirror 66.68mm Minor Axis Protected Gold



Stock #32-091 **3 In Stock**

⊖ 1 ⊕ MRP ₹50,950

● Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹50,950 each |
| Qty 6-25 | ₹40,861 each |
| Qty 26-49 | ₹38,238 each |
| Need More? | Request Quote |

Product Downloads

General

Flat Mirror **Type:**

Flatness specification is Peak to Valley **Note:**

Physical & Mechanical Properties

±0.060 **Thickness Tolerance (inches):**

| | |
|--|--|
| 15.88 ±1.52 | Thickness (mm): |
| 60.02 (Minor Axis) 84.86 (Major Axis) | Clear Aperture CA (mm): |
| ±0.015 minor, ±0.015 major | Dimensional Tolerance (inches): |
| ±0.38 | Dimensional Tolerance (mm): |
| 94.28 | Major Axis (mm): |
| 66.68 | Minor Axis (mm): |

Optical Properties

| | |
|---|--|
| 0.7 - 10 | Wavelength Range (µm): |
| Metal | Coating Type: |
| Protected Gold (700-10000nm) | Coating: |
| λ/8 | Surface Flatness (P-V): |
| 700 - 10000 | Wavelength Range (nm): |
| BOROFLOAT® | Substrate: <input type="checkbox"/> |
| R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm | Coating Specification: |
| 60-40 | Surface Quality: |
| 0.8 J/cm ² @ 1064nm, 10ns | Damage Threshold, Reference: <input type="checkbox"/> |

Regulatory Compliance

| | |
|---|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 247: |
| United States | Country of Origin: |
| Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | Imported By: |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

See Figure B in Technical Information tab for dimensional diagram.

- Circular Profile When Oriented at 45°
- Ideal for Redirecting Light
- Multiple Sizes and Coatings Offered

TECHSPEC® λ/8 Precision Elliptical Flat Mirrors are ideal for research and astronomical applications. Because of their elongated major axis, they are suited to bending and folding light at precise angles with minimum wavefront distortion. These mirrors have a circular profile when they are oriented at 45°. TECHSPEC® λ/8 Precision Elliptical Flat Mirrors feature a BOROFLOAT® substrate. Multiple sizes and coating options are offered to best suit a wide range of applications.

Technical Information

| Fig. | Minor Axis (mm) | Major Axis (mm) | Thickness (mm) | Stock No. | | | | | |
|------|-----------------|-----------------|----------------|-----------|--------------------|----------------------|-------------------|----------------|------------------|
| | | | | Uncoated | Protected Aluminum | UV Enhanced Aluminum | Enhanced Aluminum | Protected Gold | Protected Silver |
| B | 12.70 | 17.96 | 3.81 | #32-270 | #32-271 | #43-573 | #32-272 | #32-273 | #89-454 |
| B | 22.23 | 31.42 | 6.35 | #32-093 | #30-836 | #43-574 | #32-131 | #32-085 | #89-455 |
| B | 26.97 | 38.15 | 6.35 | #32-094 | #30-837 | #43-575 | #32-132 | #32-086 | #89-456 |
| A | 31.75 | 44.91 | 9.53 | #32-095 | #30-205 | #43-576 | #32-133 | #32-087 | #89-457 |
| A | 38.10 | 53.87 | 9.53 | #32-096 | #30-258 | #43-577 | #32-134 | #32-088 | #89-458 |
| A | 47.63 | 67.36 | 11.68 | #32-097 | #30-840 | #43-578 | #32-135 | #32-089 | #89-459 |
| B | 57.15 | 80.82 | 15.88 | #32-098 | #41-131 | #43-579 | #32-136 | #32-090 | #89-460 |
| B | 66.68 | 94.28 | 15.88 | #32-099 | #42-583 | #43-580 | #32-137 | #32-091 | #89-461 |
| B | 76.20 | 107.77 | 19.05 | #32-100 | #42-584 | #43-581 | #32-138 | #32-092 | #89-462 |

□