

## EO Telecentricity Test Target



Stock #58-404 **4 In Stock**

MRP ₹1,52,397

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹1,52,397 each
Qty 5+	₹1,44,804 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

110 x 156      **Pattern Size (mm):**

110 L x 110 W x 110 H      **Dimensions (mm):**

Aluminum base      **Construction:**

**Low Magnification Pattern:**  
2 alternating frequencies: 1) 3 lines, 2mm thick on 3mm centers

2) 4 lines, 0.1mm thick on 2mm centers

**Mid Magnification Pattern:**

20 lines, 0.1mm thick on 0.5mm centers

**High Magnification Pattern:**

40 lines, 0.1mm thick on 0.25mm centers

## Optical Properties

**Substrate:**

Black Print on White Mylar® with Protective Lamination

**Magnification:**

0.08X - 5X

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 240:**

[Compliant](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Critical Tool for Measurement Vision Systems
- Calibrates Any Type of Lens
- Covers Large Range of Magnifications

Telecentricity is an extremely useful metric for measuring the amount of perspective error inherent in an imaging system. Determining the degree of telecentricity allows the user to calculate an imaging system's maximum measurement accuracy. The target can be used to calibrate the degree of telecentricity in both telecentric and non-telecentric lenses. Keystoning becomes visual with the target and can be measured with software. Lenses from our 0.08X MVO® Telecentric Lens (#56-948) to the 5X Mitutoyo Telecentric Objective (#56-986), and any lens in between, including our high resolution [Double Gauss lenses](#), [VZM™ Zoom Lenses](#), and [MVO® MMS®](#) interchangeable lens system, can be calibrated or compared with this target.

### Patterns

- Low Magnification (2 Alternating Frequencies):  
3 Lines, 2mm Thickness on 3mm Centers  
4 Lines, 0.1mm Thickness on 2mm Centers
- Mid Magnification: 20 Lines, 0.1mm Thickness on 0.5mm Centers
- High Magnification: 40 Lines, 0.1mm Thickness on 0.25mm Centers

## Technical Information

