

[See all 30 Products in Family](#)

# Everix OD4 Ultra-Thin Bandpass Filter, 640nm CWL, 12.5mm Dia.

See More by [Everix](#)



Everix Ultra-Thin OD4 Bandpass Filters

Stock **#90-080** NEW CONTACT US

-
1
+
MRP ₹15,134

i Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹15,134 each
Qty 11+	₹13,621 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Flexible Filter Type:

**Physical & Mechanical Properties**

12.50 ±0.20 Diameter (mm):

>90 Clear Aperture CA (mm):

Maximum Thickness ( $\mu\text{m}$ ):  
<400

## Optical Properties

Angle of Incidence ( $^\circ$ ):  
0

Optical Density OD (Average):  
4.0

Average Transmission (%):  
>50%

Center Wavelength CWL (nm):  
640.00  $\pm$ 6.40

Full Width-Half Max FWHM (nm):  
10.00  $\pm$ 5.00

Transmission (%):  
>65 Max

Transmission Wavelength (nm):  
637.5 - 642.5 (Average)

Blocking Wavelength Range (nm):  
564.75 - 615.95; 664.35 - 715.55 (1% Transmission)

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

Country of Origin:  
United States

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Scratch Insensitive, Ultra-Thin Design
- Central Wavelengths Ranging from 400 - 1064nm
- High Average Transmission of >65%
- Narrow, 10nm Bandwidth

Everix Ultra-Thin OD4 Bandpass Filters are ultra-thin, high-performance optical components designed for precision light filtering across the visible to near-infrared spectrum. With central wavelengths ranging from 400 to 1064nm and a narrow 10nm  $\pm$  5nm FWHM, these filters offer excellent spectral selectivity and are a cost-effective alternative to traditional glass filters without compromising performance. These filters feature a <0.4 mm acrylic design, which allows for lightweight, flexible integration into a wide range of portable devices. Everix Ultra-Thin OD4 Bandpass Filters deliver exceptional durability and transmission even without anti-reflective coatings. These bandpass filters are ideal for research, sensing, and industrial applications.