

[See all 12 Products in Family](#)

**TECHSPEC® f/2.1, 25mm Focal Length Green Series M16 Lens**



25mm Focal Length, #54-855

Stock **#54-855** **20+ In Stock**

⊖ 1 ⊕ ₹5,298

**ADD TO CART**

Volume Pricing	
Qty 1+	₹5,298 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Green Series **Series:**

M12 Imaging Lens **Type:**

No **IR Cut Filter:**

Standard Lens **Imaging Lens Type:**

**Physical & Mechanical Properties**

Fixed	<b>Iris Option:</b>
24.20	<b>Length (mm):</b>
18	<b>Maximum Diameter (mm):</b>
18	<b>Outer Diameter (mm):</b>
13	<b>Weight (g):</b>

## Optical Properties

34.8mm - 14.7°	<b>Horizontal Field of View @ Max Sensor Format:</b>
Horizontal: 34.9mm - 14.7° Vertical: 26mm - 11° Diagonal: 43.9mm - 18.5°	<b>Field of View at Max Sensor Format:</b>
34.8mm - 14.7°	<b>Horizontal Field of View, 1/2" Sensor:</b>
31.5mm - 13.3°	<b>Horizontal Field of View, 1/2.5" Sensor:</b>
26.0mm - 11.0°	<b>Horizontal Field of View, 1/3" Sensor:</b>
19.4mm - 8.2°	<b>Horizontal Field of View, 1/4" Sensor:</b>
115 lp/mm @20% Contrast	<b>Resolution:</b>
8.00	<b>Maximum Image Circle (mm):</b>
0.0429	<b>Numerical Aperture NA, Object Side:</b>
4(4)	<b>Number of Elements (Groups):</b>
400 - 700	<b>Wavelength Range (nm):</b>
25.00	<b>Focal Length FL (mm):</b>
150 - ∞	<b>Working Distance (mm):</b>
f/2.1	<b>Aperture (f#):</b>
-1.69 @ Full Field	<b>Distortion (%):</b>
12.6 - 11.9	<b>Back Focal Length BFL (mm):</b>
M4 MgF <sub>2</sub> @ 580nm	<b>Coating Specification:</b>
4.43	<b>Entrance Pupil Position (mm):</b>
8.73	<b>Object Space Principal Plane (mm):</b>
-12.83	<b>Image Space Principal Plane (mm):</b>
-1.69	<b>Maximum Distortion (%):</b>
-18.02	<b>Exit Pupil Position (mm):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

1/2"	<b>Maximum Sensor Format:</b>
8.30	<b>Pixel Size (µm):</b>

## Threading & Mounting

N/A	<b>Filter Thread:</b>
M16 x 0.5	<b>Mounting Threads:</b>
M16 x 0.5	<b>Mount:</b>

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **REACH 241:**

**China** **Country of Origin:**

**Edmund Optics India Private Limited** **Imported By:**

## Product Details

- Up to 1/2", S-Mount Lens
- Up to 0.4 MegaPixels, 8.3µm Pixel Size Sensors
- Board Camera Lens Optimized for Close WD and Finite Conjugate
- 6mm to 25mm Focal Lengths


TECHSPEC® Green Series M12 Lenses designed for use in compact and board level cameras provide excellent image quality in a small, versatile package. Optimized to cover 1/3" and 1/2" sensor formats and weighing only a few grams, these machine vision lenses meet the most demanding space and weight restrictions. Each lens is threaded for M12 x0.5, except the 25.0mm focal length option ([#54-855](#)). TECHSPEC® Green Series M12 Lenses are ideal for wide angle and close focus applications, large area inspect for the automotive, forensic, pharmaceutical, and food industries. Prescription data is available by submitting a [Request for Prescription Form](#).

**Note:** Compatible [TECHSPEC M12 Imaging Lens Accessories](#) available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** **Stabilized ruggedization** versions of our Blue Series M12 Lenses, utilizing the same optics.
- **Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- **Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- **HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.


## Technical Information




#54-855, f/2.1, 25mm Focal Length Green Series M16 Lens, Distortion Plot




#54-855, f/2.1, 25mm Focal Length Green Series M16 Lens, Relative Illumination Plot



#54-855, f/2.1, 25mm Focal Length Green Series M16 Lens, Working Distance versus Field of View Plot




#54-855, f/2.1, 25mm Focal Length Green Series M16 Lens, Modulated Transfer Function (MTF) Plot, 250mm Working Distance, f2.1



#54-855, f/2.1, 25mm Focal Length Green Series M16 Lens, Depth of Field Plot, 250mm Working Distance, f2.1

Focal Length	A	B	C**	D	Mounting Thread
6.00	14.0	11.70	4.0 - 3.9	3.5	M12 x 0.5
8.00	14.0	20.40	8.9 - 8.7	6.0	M12 x 0.5
12.00	16.0	19.50	7.1 - 6.75	6.0	M12 x 0.5
25.00	18.0	24.40	12.6 - 11.9	9.0	M16 x 0.5



\*\*Minor adjustment required to match WD limits.