

[See all 30 Products in Family](#)

TECHSPEC[®] M30 x 1.0 Male to M22 x 0.75 Female Step-Down Adapter



Female M22 x0.75 to Male M30 x 1.0 Adapter, #34-771

Stock **#34-771** 1 In Stock

-

1

+

MRP ₹5,310

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹5,310 each
Qty 10-24	₹4,779 each
Qty 25-99	₹4,142 each
Need More?	Request Quote

Product Downloads

General

Type:

Thread Adapter

Physical & Mechanical Properties

Length (mm):

10.00

Outer Diameter (mm):

Threading & Mounting

Mounting Threads:
M22 x0.75 (Female) / M30 x 1

Regulatory Compliance

ViewCertificate of Conformance:

CompliantReach 240:

ChinaCountry of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

• AR Coated for Nd:YAG Laser Wavelengths: 355nm, 532nm, and 1064nm

• Fixed Magnifications Available from 2X to 10X

• Designed for OEM Integration without Divergence Adjustment

TECHSPEC® Scorpii® Nd:YAG Beam Expanders are designed for beam expansion applications such as laser engraving and material processing. These beam expanders feature AR coatings and high transmissions. AR coated for the Nd:YAG laser wavelengths 355nm, 532nm, and 1064nm, these beam expanders are available in multiple fixed magnifications from 2X to 10X with M22 x0.75 threading. TECHSPEC Scorpii Nd:YAG Beam Expanders are a cost-effective solution for system integration. Ideal for OEM quantities, these beam expanders can quickly meet prototyping and application timelines.

TECHSPEC Scorpii® Nd:YAG Beam Expander Kits are also available. For HeNe laser applications, TECHSPEC Arcturus® HeNe Beam Expanders are available. For applications where rotating optics are acceptable, the TECHSPEC Vega® Laser Line Beam Expanders and TECHSPEC Vega® Broadband Beam Expanders are available. For higher precision applications where sliding optics are necessary, please see our TECHSPEC Draconis® Nd:YAG Laser Line Beam Expanders or TECHSPEC Draconis® Broadband Beam Expanders. For broadband or ultrafast applications, TECHSPEC Canopus® Reflective Beam Expanders are available.

532nm versions are compatible with popular 530nm laser applications, and 1064nm versions are ideal for use with laser applications at 1060nm, 1070nm, and 1075nm.

